

UL1363a, Paragraph 14.1(d) States "The SPRPT shall be permanently attached to the medical equipment by a means such that it is only removable with the use of a tool." To achieve compliance, one must use the PSCLAMP.

## Safe-IT UL 1363A Medical-Grade Power Strip for Patient-Care Vicinity, 4x 15A Hospital-Grade Outlets, Safety Covers, 7 ft. Cord

MODEL NUMBER: PS-407-HG-OEM



Supplies power to movable plug-connected components mounted to IV poles, mobile carts, crash carts and mobile medical workstations in operating rooms and patient-care vicinities.

### Features

**Power Distribution Anywhere in Any Medical Facility** Ideal for use in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas For use on IV poles, mobile carts, crash carts and mobile workstations, when properly mounted 120V, 50/60 Hz power strip complies with UL 1363A specifications

**Exclusive Antimicrobial Protection** Antimicrobial coating helps resist the growth of bacteria, viruses, fungi, mold and mildew Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products

**Versatile Medical-Grade Solution** 4 NEMA 5-15R-HG hospital-grade outlets provide consistent power 7-ft. (2.13 m) power cord with NEMA 5-15P-HG hospital-grade plug provides ample reach to the power source Rugged, all-metal housing for long life in demanding environments

**Premium Safety Features** Included locking outlet safety covers block access to unused outlets Dual resettable built-in 15A circuit breakers protect against dangerous overloads Switchless design prevents accidental shutoff

**Ready to Use Right Out of the Box** Built-in mounting tabs and flanges for easy installation on a variety of surfaces

## Specifications

### OVERVIEW

### Highlights

- Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew
- Approved for use in patient-care vicinities when properly mounted
- Complies with UL 1363A specifications
- 4 NEMA 5-15R-HG outlets with locking safety covers
- 7 ft. (2.1 m) cord with NEMA 5-15P-HG plug reaches nearby outlets

### Package Includes

- PS-407-HG-OEM UL 1363A Medical-Grade Power Strip, 7-ft. (2.13 m) cord
- Owner's manual



UPC Code	037332203632
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V
Input Plug Features	Hospital Grade Plug
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	7
Input Cord Length (m)	2.13
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	2 x 15amp breakers (1 line, 1 neutral)
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	No power switch
<b>PHYSICAL</b>	
Material of Construction	Metal
Color	White
Power Cord Color	White
Form Factors Supported	IV poles, mobile carts, crash carts and mobile medical workstations
Housing Color	White
Included Mounting Accessories	Mounting tabs and flanges
Mounting Holes or Slots	Yes
Outlets Measurement (Center to Center)	Inner outlets = 32.5mm
Receptacle Color	White



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Shipping Dimensions (hwd / cm)	5.59 x 15.49 x 24.89
Shipping Dimensions (hwd / in.)	2.20 x 6.10 x 9.80
Shipping Weight (kg)	1.04
Shipping Weight (lbs.)	2.30
Unit Dimensions (hwd / in.)	8.65 x 2.5 x 1.5
Unit Dimensions (hwd / cm)	21.97 x 6.35 x 3.81
Unit Weight (lbs.)	2.77
Unit Weight (kg)	1.26
Mounting Details	Includes flanges
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	Yes
Built-in Cable Management	No
Built-In Circuit Breaker	Yes
Antibacterial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Approvals	TUV tested to UL 1363A
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>