

Safe-IT UK BS-1363 Medical-Grade Power Strip with 4 UK Outlets, 3 m Cord

MODEL NUMBER: PS410HGUK



Distributes power to plug-connected components inside and outside patient care vicinities, including examining rooms.

Features

Power Distribution Anywhere in Any Medical Facility This 230V, 50/60 Hz medical-grade power strip supplies electricity to plug-connected components in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas. Compliant with BS-1363 specifications, the PS410HGUK features a three-meter (10-foot) UK power cord with 13A fused Type G plug and four UK outlets.

Exclusive Antimicrobial Protection Fights Healthcare-Acquired Infections (HAIs) The power strip is protected by a patented antimicrobial powder coating with EPA-registered and FDA-compliant silver ionic technology. The antimicrobial surface protection is 99.9 percent effective in inhibiting the growth of bacteria and reducing the risk of HAIs in hospitals and other medical environments. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Armed with the Latest Safety Features to Protect Valuable Equipment A built-in replaceable 13A fuse controls all four outlets and protects against overloads by shutting them down if the equipment load draws too much power. The switchless design prevents the unit from being accidentally shut off, which would cut essential power to all connected devices. A green mains indicator lights to signal the power strip is properly connected to an AC power source.

Long Cord Provides Enhanced Mobility The three-meter UK power cord allows for optimum flexibility when putting together a mobile health care workstation. The PS410HGUK can be mounted in a different area from where it draws AC power, putting you in control of getting reliable power service where you need it most. For best performance, connect the Type G plug to a standard 13A isolated ground receptacle to eliminate unwanted ground noise.

Equipotential Grounding Helps Your Equipment Perform at Its Best The included M5 earth ground stud and 250-millimeter-long earth wire help reduce unwanted leakage currents between connected devices.

Comes Ready to Install and Use Right Out of the Box Built-in mounting tabs and flanges let you install the PS410HGUK on a wide variety of surfaces, including IV poles, mobile carts, crash carts and mobile medical workstations. The durable all-metal housing is designed to last a long time in demanding work environments.

Highlights

- Meets BS-1363 specifications for use inside and outside patient-care vicinities
- Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew
- Replaceable 13A fuse shuts down all 4 UK outlets in case of overload
- Mounting tabs/flanges for installation on IV poles, mobile carts and crash carts
- Switchless design protects connected devices from dangerous accidental shutdowns

Applications

- Medical-grade power distribution for IV poles, mobile carts, crash carts and mobile medical workstations inside and outside operating rooms and other patient-care vicinities

Package Includes

- PS410HGUK UK BS-1363 Medical-Grade Power Strip with 4 UK Outlets, 10-ft. (3.05 m) Cord
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332203243
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	13A 230V
Input Connection Type	BS1363
Input Plug Features	Hospital Grade Plug
Voltage Compatibility (VAC)	230
Input Plug Type	BS1363
Input Cord Length (ft.)	10
Right-Angle Plug	No
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) British BS 1363A
Circuit Breaker (amps)	13
Overload Protection	13A in plug fuse
Outlet Orientation	Single row of 4
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
Audible Alarm	NO ALARM
PHYSICAL	
Color	Beige
Material of Construction	Metal
Power Cord Color	White
Form Factors Supported	IV poles, mobile carts, crash carts and mobile medical workstations
Included Mounting Accessories	Mounting tabs and flanges
Mounting Holes or Slots	Yes



Powering Business Worldwide



Receptacle Color	White
Shipping Dimensions (hwd / in.)	3.94 x 6.97 x 17.52
Shipping Dimensions (hwd / cm)	10.01 x 17.70 x 44.50
Shipping Weight (lbs.)	3.66
Shipping Weight (kg)	1.66
Unit Dimensions (hwd / in.)	1.810 x 2.990 x 13.700
Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Antimicrobial	Yes
Built-In Circuit Breaker	Yes
Antibacterial	No
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.