

Product Use in your Country or Municipality

Tripp Lite Healthcare Product Specialist

Safe-IT Medical-Grade Power Strip, UL 1363, 4 Hospital-Grade Outlets, Antimicrobial, 15 ft. (4.57 m) Cord

MODEL NUMBER: **PS-415-HG**



Medical-grade power strip with patented antimicrobial coating and long 15 ft. cord provides safe, versatile power distribution.

Description

The PS-415-HG Medical-Grade Power Strip supplies power outside of patient-care vicinities, such as administrative areas or in resident rooms of long-term care facilities that do not use line-operated electrical equipment for diagnostic, treatment or monitoring purposes. Compliant with UL 1363 specifications, this 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and four NEMA 5-15R-HG hospital-grade outlets.

The power strip is protected by a antimicrobial powder coating. Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

A built-in resettable 15A circuit breaker controls power to all outlets and protects the power strip against overloads. Switchless design prevents the unit from being accidentally shut off. The 15-foot (4.6 m) cord provides ample reach to a power source.

Keyhole mounting tabs and flanges make installing this power strip easy. The all-metal housing ensures safety and is guaranteed to last a long time in demanding surroundings.

Features

Power Distribution Outside of Patient-Care VicinitiesIdeal for use in administrative areas and resident rooms with no line-operated electrical equipment for diagnostic, treatment or monitoring purposes120V, 50/60 Hz power strip complies with UL 1363 specifications

Exclusive Antimicrobial ProtectionAntimicrobial coating helps resist the growth of bacteria, viruses, fungi, mold and mildewCoating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Versatile Medical-Grade Solution4 NEMA 5-15R-HG hospital-grade outlets provide consistent powerRugged, all-metal housing for long life in demanding environments

Highlights

- Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew
- Complies with UL 1363 specifications
- 15 ft. (4.6 m) cord with NEMA 5-15P-HG hospital-grade plug
- Features 4 NEMA 5-15R-HG hospital-grade outlets

Package Includes

- PS-415-HG UL 1363 Medical-Grade Power Strip with four 15A Hospital-Grade Outlets and 15-ft. (4.57 m) Cord
- Owner's Manual

Premium Safety Features Resettable 15A circuit breaker protects against dangerous overloads Switchless design prevents accidental shut-off

Ready to Use Right Out of the Box Built-in keyhole mounting tabs and flanges make the PS-415-HG easy to install on a variety of surfaces

Specifications

OVERVIEW	
UPC Code	037332118479
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Plug Features	Hospital Grade Plug
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	
Color	White
Material of Construction	Metal
Power Cord Color	White

Housing Color	White
Included Mounting Accessories	Keyhole mounting tabs and flanges
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45mm
Outlets Measurement (Center to Center)	Inner outlets = 32.5mm
Receptacle Color	White
Shipping Dimensions (hwd / in.)	2.40 x 5.90 x 10.00
Shipping Dimensions (hwd / cm)	6.10 x 14.99 x 25.40
Shipping Weight (lbs.)	3.00
Shipping Weight (kg)	1.36
Unit Dimensions (hwd / in.)	2.000 x 5.500 x 10.000
Unit Dimensions (hwd / cm)	3.8 x 21.9 x 6.4
Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Antimicrobial	Yes
Rotatable Outlets	No
Built-in Cable Management	No
Built-In Circuit Breaker	Yes
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty