

4-Outlet Power Strip with USB-A Charging - BS1363A Outlets, 220-250V, 13A, 1.8 m Cord, BS1363A Plug, White

MODEL NUMBER: PS4B18USBW



4-outlet power strip with USB-A ports distributes electricity to home and office electronics and charges your mobile devices.

Features

35.6 cm Power Strip Delivers Electricity to 4 Devices at the Same Time Compatible with standard electrical equipment, this Protect It!® power strip features four BS1363A outlets and a durable white plastic housing. It is ideal for powering almost anything with a compatible plug, including computers and mobile devices to appliances and power tools.

Charges 2 Mobile Devices with 2.1A of Shared Power In addition to AC outlets, this power strip provides USB charging for up to two mobile devices, including smartphones, tablets and e-readers. The USB-A ports eliminate the need for AC adapters for charging cords, leaving outlets available for AC equipment.

Designed to Give You Flexibility in Placing the Power Strip Where It's Most Needed The power strip features a space-saving right-angle BS1363A plug that helps you connect to a wall outlet located behind furniture that is placed flush against the wall. The plug is attached to a 1.8-meter power cord, which gives you more choices in placing the power strip away from the connected AC outlet.

Vertical or Horizontal Mounting for Desks and Workbenches Keyhole-shaped mounting slots on the back of the power strip allow you to permanently install it on any flat surface, including walls, with user-supplied hardware.

Premium Safety Features Designed for Protecting Your Valuable Equipment The PS4B18USBW features an on/off switch with diagnostic LED that provides one-touch control over all connected devices. A built-in 13-amp circuit breaker immediately shuts down the entire power strip in case of an overload to prevent equipment damage.

Highlights

- 4 BS1363A outlets distribute power to appliances, tools, lighting and other electronics
- 1.8 m cord with BS1363A plug offers flexible placement in relation to an AC wall outlet
- 2 USB-A ports share 2.1A of power for charging phones, tablets and other mobile devices
- Rear keyhole slots enable mounting to desk or workbench for easy access to outlets
- 13A circuit breaker shuts down all UK outlets for safety in case of overload

Applications

- Distribute power to computer equipment and other devices in an office, workbench, retail or telecom environment
- Mount a power strip to the edge of a desk or workbench for easy access to outlets
- Charge a smartphone and tablet without taking up available AC outlets

Package Includes

- PS4B18USBW 4-Outlet Power Strip, British BS1363A Outlets, White

Specifications

OVERVIEW	
UPC Code	037332251602



Product Type	Power Strip
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250
Input Plug Type	British
Right-Angle Plug	Yes
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) British BS 1363A
Circuit Breaker (amps)	13
Overload Protection	combo switch/circuit breaker
Outlet Orientation	right-angled
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Two position power switch
SURGE / NOISE SUPPRESSION	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
Automatic Shut-Off	No
CHARGING	
Charging Ports / Amps	(2) 2.1A
Number of Charging Ports	2
Charging Method	USB
Charging Port Type	USB A (FEMALE)
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No



Network (Ethernet) Protection	No
PHYSICAL	
Color	White
Antimicrobial Coating	No
Color (AC Line Cord)	White
Housing Color	White
Integrated Keyhole Mounting Slots	Yes
Material of Construction	Plastic
Receptacle Color	White
Shipping Dimensions (hwd / cm)	35.56 x 8.64 x 7.37
Shipping Dimensions (hwd / in.)	14.00 x 3.40 x 2.90
Shipping Weight (kg)	0.44
Shipping Weight (lbs.)	0.98
Unit Dimensions (hwd / cm)	11.6 x 2.9 x 2.9
Unit Dimensions (hwd / in.)	29.5 x 7.5 x 6.5
Unit Weight (kg)	0.37
Unit Weight (lbs.)	0.81
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Approvals	CE, RoHS, Reach
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>