

Industrial Power Strip, 6-Outlet, 4 ft. (1.2 m) Cord

MODEL NUMBER: PS6



Highlights

- 6 outlets
- 4-ft. (1.22 m) cord
- 9.5-inch length
- Master on/off switch

Package Includes

- PS6 Power Strip
- Warranty information
- Instruction manual

Description

The PS6 Power Strip offers a convenient method of power distribution in workbench, wall-mount or floor-mount applications. Includes six NEMA 5-15R outlets, 4-ft. (1.22 m) AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes the PS6 ideal for distributing alternate waveform UPS or generator power. Features power switch, circuit breaker and attractive gray color scheme.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 6 NEMA 5-15R

ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT - Corded power distribution strip

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles
- Power switch
- 15A circuit breaker
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15A power handling capacity
- 4-ft. (1.22 m) AC line cord

Specifications

OVERVIEW	
UPC Code	037332116123
INPUT	
Nominal Input Voltage(s) Supported	120V AC



Powering Business Worldwide



Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	4
Right-Angle Plug	No
Input Cord Length (m)	1.22
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Master on/off switch with separate circuit breaker
PHYSICAL	
Color	Light Gray
Material of Construction	Plastic
Power Cord Color	Light Gray
Housing Color	Gray
Mounting Holes or Slots	Yes
Receptacle Color	Light gray
Shipping Dimensions (hwd / in.)	10.60 x 2.00 x 3.60
Shipping Dimensions (hwd / cm)	26.92 x 5.08 x 9.14
Shipping Weight (lbs.)	0.83
Shipping Weight (kg)	0.38
Unit Dimensions (hwd / in.)	1.200 x 1.700 x 9.450
Unit Dimensions (hwd / cm)	3.05 x 4.32 x 24.01
Unit Weight (lbs.)	.77
Unit Weight (kg)	0.35
FEATURES & SPECIFICATIONS	



Powering Business Worldwide



Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.