

Safe-IT UL 1363A Medical-Grade Power Strip for Patient Care Vicinities, 6 Hospital-Grade Outlets, Load Monitor, Safety Covers, Antimicrobial, 7 ft. (2.1 m) Cord

MODEL NUMBER: PS-607-HG-OEMLM



Delivers power to medical equipment attached to IV poles, crash carts and mobile workstations in operating rooms and other patient care vicinities.

Features

Medical-Grade Power Strip Approved for Patient Care Vicinities

The PS-607-HG-OEMLM features six NEMA 5-15R-HG “green dot” hospital-grade outlets that supply power to equipment mounted to IV poles, mobile carts, crash carts and mobile medical workstations inside and outside patient care vicinities. Compliant with UL 1363A specifications, this power strip can be used in patient rooms, operating rooms, therapy rooms, dialysis rooms, labs, and assisted living and home health environments.

Monitor Your Power Load to Remain Within NFPA 99 Guidelines

This power strip features an electronic two-digit load monitor that lets you know if the strip is close to reaching or exceeding National Fire Protection Association (NFPA) 99 standards (“The sum of the ampacity of all appliances connected to the outlets does not exceed 75 percent of the ampacity of the flexible cord supplying the outlets.”). If the rated cord current exceeds the NFPA 99 limit, the load monitor flashes and switches colors to catch your attention from a distance without creating alarm fatigue.

Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Work Environment

The Safe-IT™ power strip features antimicrobial protection that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

Premium Safety Features Help Ensure Proper Power Connections

With no central power switch, this power strip presents no danger of accidental shutoff and cutting off power to essential devices. Two resettable circuit breakers will shut down all AC input if the power strip determines the connected equipment load is drawing too much power. Plastic safety covers block access to unused outlets.

Ready for Installation in Demanding Medical Environments

The seven-foot (2.1-meter) cord with NEMA 5-15P-HG “green dot” plug connects to a wall outlet. Built-in mounting flanges let you install the durable all-metal housing on any mobile cart or IV pole (using PSCLAMP, sold separately) for distributing power to movable rack-, table- and pedestal-mounted equipment. Scan the Easy Asset QR code on the side of the power strip to access product resources and other critical information.

Highlights

- UL 1363A power strip approved for use inside and outside patient care vicinities
- Electronic load monitor measures rated cord current for NFPA 99 safety
- 6 NEMA 5-15R-HG outlets feature plastic locking covers for protection
- Switchless design helps prevent accidental shutdown of essential equipment
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

Package Includes

- PS-607-HG-OEMLM UL 1363A Medical-Grade Power Strip, 6 Outlets, 7 ft. (2.1 m) Cord
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Specifications

OVERVIEW	
UPC Code	037332287694
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Connection Type	NEMA 5-15P-HG
Input Plug Features	Hospital Grade Plug
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	7
Right-Angle Plug	No
Input Cord Length (m)	2.13
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	2 x 15amp breakers (1 line, 1 neutral)
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	No power switch
Diagnostic LED Details	NORMAL OPERATING CONDITION: BLUE LED DISPLAY ; EXCEEDS OPERATING CONDITION: FLASHING RED LED DISPLAY
PHYSICAL	
Color	White
Material of Construction	Metal
Power Cord Color	White



Powering Business Worldwide

TRIPP LITE
SERIES

Form Factors Supported	IV poles, mobile carts, crash carts and mobile medical workstations
Housing Color	White
Included Mounting Accessories	Mounting tabs and flanges
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between keyhole slots = 261.92mm; Distance between end tabs = 330.17mm
Outlets Measurement (Center to Center)	1.52 in.
Receptacle Color	White
Shipping Dimensions (hwd / in.)	14.17 x 5.98 x 2.17
Shipping Dimensions (hwd / cm)	35.99 x 15.19 x 5.51
Shipping Weight (lbs.)	3.26
Shipping Weight (kg)	1.48
Unit Dimensions (hwd / in.)	13.630 x 2.500 x 1.840
Unit Weight (lbs.)	2.4
Unit Weight (kg)	1.09
Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	Yes
Built-In Circuit Breaker	Yes
Antibacterial	No
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 1363A
Product Compliance	NFPA 99: 10.2.3.6; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://triplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.