

## Power It! 6-Outlet Power Strip, 15 ft. (4.57 m) Cord

MODEL NUMBER: **PS615**



### Highlights

- 6 outlets
- Illuminated on/off switch
- 15-amp circuit breaker
- 15-ft. (4.57 m) power cord
- Keyhole mounting slots

### Package Includes

- PS615 power strip
- Warranty information
- Instruction manual

### Description

Tripp Lite's Power It! PS615 power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. Includes 6 NEMA 5-15R outlets, 15-ft. (4.57 m) AC power cord and keyhole mounting slots. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features illuminated power switch and 15A integrated circuit breaker to prevent dangerous overloads.

INPUT/OUTPUT: Input: NEMA 5-15P/Output: 6 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: Corded power distribution strip

### Features

- 6 outlets
- 15-ft. (4.57 m) cord
- 15 amp resettable circuit breaker
- Can accommodate 1 large transformer plug without covering remaining outlets, 3 total transformers
- Keyhole support for wall mounting
- Lighted power switch
- 120V AC, 50/60Hz electrical compatibility
- UL certification

## Specifications

OVERVIEW	
UPC Code	037332175557



<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Illuminated on/off switch controls power to all outlets
<b>PHYSICAL</b>	
Color	Light Gray
Material of Construction	Plastic
Antimicrobial	No
Power Cord Color	Light Gray
Housing Color	Light Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between slots = 101mm, distance between slot height = 28mm
Outlets Measurement (Center to Center)	28.5mm
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	33.27 x 5.08 x 15.24
Shipping Dimensions (hwd / in.)	13.10 x 2.00 x 6.00



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Shipping Weight (kg)	0.91
Shipping Weight (lbs.)	2.00
Unit Dimensions (hwd / in.)	10.8 x 1.85 x 1.23
Unit Dimensions (hwd / cm)	27.43 x 4.70 x 3.12
Unit Weight (lbs.)	1.6
Unit Weight (kg)	0.73
<b>STANDARDS &amp; COMPLIANCE</b>	
Canada	cUL
Additional International Approvals	Complies with RoHS (Restriction of Hazardous Substances Directive)
UL1363 (Power Tap)	UL1363
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>