

24-Outlet Vertical Power Strip, 120V, 20A, Hardwired Input, 72 in.

MODEL NUMBER: **PS7224-20HW**



Highlights

- AC input hardwired via knockout on unit
- 24 outlets
- Ideal for applications requiring permanent installation

Package Includes

- PS7224-20HW
- Instruction manual

Description

Tripp Lite's PS7224-20HW Power Strip offers 20 amp multi-outlet AC power distribution in a convenient 72 inch hardwire cabinet. Includes knockout panels to accept 3/4 in. conduit fittings for hardwire installation and 24 output receptacles with 2.795 inch center-to-center spacing. Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications.

INPUT/OUTPUT: Input: Hard-wire access via knockout panels that accept 3/4 inch conduit fittings

Output: 24 outlets total, 2 NEMA 5-15/20R (20A) and 22 NEMA 5-15R (15A)

ELECTRICAL: 120V AC, 50/60Hz, 20A (no circuit breaker)

FORMAT: 72 inch strip format with 24 outlets

Features

- Versatile all-metal 72 inch format with outlets arranged in a single row
- Knockout panels for 3/4 inch conduit fittings allow permanent hardwire installation
- Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications
- 24 outlets total, 2 NEMA 5-15/20R (20A) and 22 NEMA 5-15R (15A)
- 20 amp electrical capacity
- 120V AC, 50/60Hz electrical compatibility

Specifications

OVERVIEW	
UPC Code	037332042361
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A 120V

Voltage Compatibility (VAC)	120
Input Plug Type	Hard-wire
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(2) 5-15/20R; (22) 5-15R
Circuit Breaker (amps)	20
Transformer Accommodation	(12) Yes
Right-Angle Outlets	No
Outlet Spacing	2.795 in.
PHYSICAL	
Color	Beige
Material of Construction	Metal
Housing Color	Beige
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	101.60mm
Receptacle Color	Beige
Shipping Dimensions (hwd / in.)	2.80 x 2.60 x 76.50
Shipping Dimensions (hwd / cm)	7.11 x 6.60 x 194.31
Shipping Weight (lbs.)	7.60
Shipping Weight (kg)	3.45
Unit Dimensions (hwd / in.)	1.490 x 1.490 x 72.000
Unit Dimensions (hwd / cm)	182.88 x 3.8 x 3.8
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed

Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty