

UPS Replacement Battery Cartridge Kit (2 sets of 2) for select APC UPS

MODEL NUMBER: RBC11A



Highlights

- Up to 30% longer runtime than basic replacements
- OEM certified premium batteries
- Rugged, leakproof construction
- Maintenance-free
- Wide operating temperature range

Package Includes

- UPS battery replacement cartridge
- Instruction manual with installation, recycling and warranty information

Description

Tripp Lite's premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery set is carefully configured to meet or exceed all of the original manufacturer specifications and ships pre-assembled and ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. Compatible with select UPS systems from APC and other major brands. See Tripp Lite's UPS replacement battery page to confirm compatibility and quantity required.

Features

- Restores your UPS to its original runtime specifications
- Comes pre-assembled and ready for installation into your UPS system
- Reusable packaging holds expired batteries for recycling center delivery
- Compatible with many brands and models, including APC models SU1400XLNET, SU1400RMXLNET, SU2200, SU2200NET, SU2200RM, SU2200RMNET, SU2200RMXL, SU2200RMXLT, SU2200XLNET, SU2200XLNET, SU3000, SU3000NET, SU3000RM, SU3000RMNET, SU24XLBP, SU48XLBP, and SU48BP

Specifications

OVERVIEW	
UPC Code	037332118455
BATTERY	
Included Battery Set	Contains (4) 12V 17AH sealed lead acid batteries
Typical Battery Lifespan	3 - 5 years, depending on host UPS operating conditions
PHYSICAL	

Shipping Dimensions (hwd / in.)	26.71 x 9.25 x 17.25
Shipping Dimensions (hwd / cm)	67.84 x 23.50 x 43.82
Shipping Weight (lbs.)	58.00
Shipping Weight (kg)	26.31
Unit Dimensions (hwd / in.)	6.800 x 5.600 x 7.200
Unit Dimensions (hwd / cm)	Includes 2 batteries; Each measures 16.669 x 14.922 x 17.78
Unit Weight (lbs.)	58
Unit Weight (kg)	26.31
ENVIRONMENTAL	
Relative Humidity	0 - 95% non-condensing
Operating Elevation (ft.)	0 - 10,000 feet
Storage Elevation (ft.)	0 - 50,000 feet
Operating Elevation (m)	0-3000 m
Storage Elevation (m)	0 - 15,200 m
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty