

# UPS Replacement Battery Cartridge for SUINT1000LCD2U UPS System, 24V

MODEL NUMBER: RBC24S



UPS backup battery replacement breathes new life into a Tripp Lite UPS system suffering from expired or weak internal batteries.

## Features

### UPS Replacement Battery Cartridge for SUINT1000LCD2U UPS System

This UPS backup battery replacement is carefully screened and certified to meet or exceed original specifications. The leakproof, no-maintenance RBC24S comes pre-assembled and pre-wired as two 12V batteries for quick and easy installation in your SUINT1000LCD2U. It functions within a wide range of operating temperatures. A sensor automatically informs the UPS that the battery has been replaced, so the UPS can reset the battery age. Reusable packaging allows you to easily send expired batteries to a recycling center.

## Highlights

- Replacement battery backup for SUINT1000LCD2U UPS system
- Carefully screened and certified to restore UPS runtime to original specs
- Leakproof internal battery requires no regular maintenance
- Ships fully assembled and ready for immediate installation to prevent downtime
- Auto-detection sensor allows UPS to reset internal battery age

## Applications

- Replace the aging or expired internal battery in your Tripp Lite SUINT1000LCD2U UPS system

## System Requirements

- Compatible with SUINT1000LCD2U UPS system

## Package Includes

- RBC24S UPS Battery Replacement (pre-assembled battery pack with two 12V batteries)

## Specifications

OVERVIEW	
UPC Code	037332239372
BATTERY	
DC System Voltage (VDC)	24
Included Battery Set	Contains (2) 12V 9AH sealed lead acid batteries
Typical Battery Lifespan	3 to 5 years typical, depending on UPS operating conditions
PHYSICAL	
Shipping Dimensions (hwd / in.)	5.51 x 12.00 x 8.86
Shipping Weight (kg)	6.50
Unit Dimensions (hwd / in.)	2.640 x 5.950 x 7.910
Unit Dimensions (hwd / cm)	6.71 x 15.11 x 20.09



Powering Business Worldwide



Unit Weight (lbs.)	14.33
Unit Weight (kg)	6.50
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.