

# UPS Replacement Battery Cartridge (Set of 16 Batteries) for Select SmartOnline UPS Systems, 192VDC, 3U

MODEL NUMBER: RBC58-3US



UPS backup battery replacement breathes new life into a Tripp Lite UPS system suffering from expired or weak internal batteries.

## Features

### UPS Replacement Battery Cartridge for Select UPS Systems

This premium set of 16 pre-wired 12V 5Ah batteries (two 96V battery trays) is designed for UPS models specifying its use (see *System Requirements* below for a list). The RBC58-3US has been carefully screened and certified to meet or exceed original runtime specifications. The leakproof, no-maintenance backup battery comes pre-assembled for quick installation in your UPS system without potentially costly downtime, and it operates within a wide range of temperatures. Reusable packaging makes it easy for you to send the expired batteries to a recycling center.

## Highlights

- Maintenance-free battery backup for select UPS systems (see *System Requirements*)
- Carefully screened and certified to meet or exceed original UPS specs
- Reusable packaging holds expired batteries for recycling center delivery
- Ships fully assembled and ready for immediate installation to prevent downtime

## System Requirements

Designed for use with the following UPS systems and external battery packs:

- UPS Models with Built-In Receptacles: SU5KRT3UHV, SU5KRT3UX, SU5KRT3UG, SU5KRT3UHW, SU5KRT3UTF, SU6KRT3UHV, SU6KRT3UTF, SU6KRT3UX, SU6KRT3UG, SU6KRT3UHW
- UPS Models with a Detachable Bypass Power Distribution Module: SU5KRT3UHVMB, SU5KRT3UTFMB, SU5KRT3UGMB, SU5KRT3UHVMB, SU6KRT3UHVMB, SU6KRT3UHFMB, SU6KRT3UGMB, SU6KRT3UHVMB, SU6KRT3UXMB
- External Battery Packs: BP192V12RT3US

## Package Includes

- RBC58-3US UPS Battery Replacement Cartridge (16 pre-wired batteries)
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332251275
BATTERY	
DC System Voltage (VDC)	192
Typical Battery Lifespan	3 to 5 years, depending on UPS operating conditions



Powering Business Worldwide



PHYSICAL	
Rack Height	3U
Minimum Required Rack Depth (cm)	66.04
Minimum Required Rack Depth (inches)	26
Unit Dimensions (hwd / in.)	3.740 x 4.700 x 22.540
Unit Dimensions (hwd / cm)	21.2 x 18 x 14
Unit Weight (lbs.)	71.4
Unit Weight (kg)	32.39
Rack Units	3
ENVIRONMENTAL	
Relative Humidity	0-95% non-condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
 Eaton is a registered trademark. All other trademarks  
 are the property of their respective owners.