

# Replacement Battery Cartridge for Select 72V SmartOnline UPS Systems

MODEL NUMBER: RBC72S



Extends the battery life of select Tripp Lite SmartOnline UPS systems.

## Description

The RBC72S Replacement Battery Cartridge breathes new life into select UPS systems whose internal batteries are expired or not working. Built to function in a wide range of operating temperatures, the RBC72S has been carefully screened and certified to restore your UPS system's runtime performance to its original specifications. The leakproof, no-maintenance RBC72S comes preassembled and prewired for quick and easy installation in your UPS system. Reusable packaging holds expired batteries for delivery to the nearest recycling center. Compatible with SU3000RTXL2U (LED display to the right of front bezel), SU3000RTXLCD2U, SU3000LCD2UHV, SUINT3000LCD2U, SUINT3000RTXL2U (LED display to the right of front bezel) and other models recommending its use.

## Features

### Replacement Internal Battery for Select UPS Systems

- Screened and certified to restore UPS system's runtime performance to original specs
- compatible with SU3000RTXLCD2U, SU3000LCD2UHV, SUINT3000LCD2U and other models recommending its use
- Preassembled and prewired for immediate installation
- Designed for a wide range of operating temperatures
- Rugged leakproof construction
- No maintenance required
- Reusable packaging for delivering expired batteries to recycling center

## Highlights

- Replacement internal battery for select UPS systems
- Rugged leakproof construction
- No maintenance required
- Wide range of operating temperatures
- Preassembled and prewired for immediate installations

## Package Includes

- RBC72S Replacement 72V Battery Cartridge

## Specifications

OVERVIEW	
UPC Code	037332189172
BATTERY	
DC System Voltage (VDC)	72



Powering Business Worldwide



Included Battery Set	Contains (6) 12V 9AH sealed lead acid batteries
Typical Battery Lifespan	3 to 5 years, depending on UPS operating conditions
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	5.50 x 12.00 x 21.26
Shipping Dimensions (hwd / cm)	13.97 x 30.48 x 54.00
Shipping Weight (lbs.)	39.68
Shipping Weight (kg)	18.00
Unit Dimensions (hwd / in.)	2.660 x 8.340 x 17.910
Unit Dimensions (hwd / cm)	6.76 x 21.18 x 45.49
Unit Weight (lbs.)	37.26
Unit Weight (kg)	16.90
<b>ENVIRONMENTAL</b>	
Relative Humidity	0-95% non-condensing
Operating Elevation	0-10000 ft. (0-3000 m)
Storage Elevation (ft.)	10,000 ft.
Storage Elevation (m)	3000 m
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
 Eaton is a registered trademark. All other trademarks  
 are the property of their respective owners.