

1U Rack-Mount Power Strip, 120V, 20A, 5-20P, 12 Outlets (6 Front-Facing, 6-Rear-Facing) 15 ft. (4.57 m) Cord

MODEL NUMBER: RS-1215-20



Highlights

- Designed for standard 19-inch racks (1U high)
- 12 outlets (6 front / 6 rear)
- 15-ft. (4.57 m) cord
- 20-amp circuit breaker

Package Includes

- RS-1215-20
- Warranty information
- Instruction manual

Description

Tripp Lite's RS-1215-20 Power Strip offers 20 amp capacity AC power distribution in a versatile multi-mount cabinet. Detachable mounting flanges are configurable for rackmount, wallmount and under-counter installation. Uses only 1 rack space (1U) when installed in any 19 inch rack meeting EIA standards. Unfiltered electrical pass-through makes RS-1215-20 ideal for distributing alternate waveform UPS or generator power in rack enclosures, network closets and more. Includes 12 NEMA5-20R outlets (6 front/6 rear), 15-ft. (4.57 m) AC power cord and lighted switch with cover prevents risk of accidental turn-off.

PLUG/OUTLET: Input: NEMA 5-20P

Output: 12 NEMA5-20R (6 front & 6 rear)

ELECTRICAL: 120V AC, 50/60Hz, 20A (Requires NEMA 5-20R wall receptacle)

FORMAT: 19 in. rackmount (uses 1 rack space/1U), wallmount, under-counter and more

Features

- Versatile all-metal cabinet with detachable mounting flanges allows rackmount, wallmount, undercounter and other creative mounting options
- Uses one rack space (1U) in standard 19 inch rack ("zero U" mounting possible in many racks)
- Unfiltered electrical pass-through reliably distributes alternate waveform AC power from UPS or generator to supported equipment
- 12 NEMA5-20R output receptacles (6 front/6 rear)
- 15-ft. (4.57 m) AC cord NEMA5-20P plug connection
- Lighted power switch confirms power on/off status
- Snap-in switch guard prevents accidental turn off
- 20 amp electrical capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility



Specifications

OVERVIEW	
UPC Code	037332099372
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A 120V
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-20P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	2400
Output Receptacles	(12) 5-15/20R
Circuit Breaker (amps)	20
Transformer Accommodation	(3) Yes
Outlet Orientation	6 front facing / 6 rear facing
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Red illuminated 2 position switch controls power to all outlets
Locking Switch Cover	Transparent locking switch cover prevents accidental shutoff
PHYSICAL	
Color	Black
Antimicrobial Coating	No
Color (AC Line Cord)	Black
Form Factors Supported	1U rackmount, wall-mount and undercounter installation supported
Included Mounting Accessories	Rackmount flanges
Integrated Keyhole Mounting Slots	No
Material of Construction	Metal
Outlets Measurement (Center to Center)	Distance between Front outlets = 51.6mm; Distance between Rear outlets = 71.1mm



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Receptacle Color	Black
Shipping Dimensions (hwd / cm)	23.37 x 6.60 x 51.56
Shipping Dimensions (hwd / in.)	9.20 x 2.60 x 20.30
Shipping Weight (kg)	2.77
Shipping Weight (lbs.)	6.11
Unit Dimensions (hwd / cm)	4.445 x 44.45 x 11.4
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 4.5
Unit Weight (kg)	2.09
Unit Weight (lbs.)	4.6
SPECIAL FEATURES	
TVSS Grounding	Back panel nut and bolt grounding lug
STANDARDS & COMPLIANCE	
Canada	cUL
UL1363 (Power Tap)	UL1363 (UR status)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>