



Powering Business Worldwide

SCSI/Fibre Channel - 68-in. Internal SCSI III Fast/Wide Ribbon Cable 8Conn HD68M

MODEL NUMBER: S034-68I



Highlights

- Premium cabling

System Requirements

- Wide SCSI controller
- Wide SCSI drive or internal device

Package Includes

- 68-in. internal SCSI III fast/wide ribbon cable 8Conn HD68M

Description

This 68 inch SCSI III internal ribbon cable is used to connect up to 7 fast/wide SCSI devices to the SCSI host controller card. These devices require HD68M connectors and commonly include CD-ROM and hard drives. This cable has 8 high quality HD68M connectors: one for the SCSI host adapter and 7 for device connections. This cable is configured for use in most towers. The length of cable between the host controller and the first device is 20 inches and each device connector is spaced 8 inches apart. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- 68-in. long
- Supports transfer speeds up to 40Mbps
- Eight 68pin male (HD68M) fast/ wide SCSI connectors
- Internal 68in (5.8ft) 68pin wide SCSI ribbon cable with 8 connections used to connect internal devices requiring HD68M interface
- All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest Ultra 320 to legacy SCSI-1 and every combination in between
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

Specifications

OVERVIEW	
UPC Code	037332013804
Drives Supported	7
Technology	Ribbon/Internal; SCSI
CONNECTIONS	



Powering Business Worldwide

Side A - Connector 1	INTERNAL HD68 (MALE)
Side B - Connector 1	INTERNAL HD68 (MALE)
PHYSICAL	
Cable Length (ft.)	5.7
Cable Length (m)	1.74
Cable Length (in.)	68
Shipping Dimensions (hwd / in.)	11.75 x 7.00 x 1.50
Shipping Dimensions (hwd / cm)	29.84 x 17.78 x 3.81
Shipping Weight (lbs.)	0.47
Shipping Weight (kg)	0.21
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.