

SCSI Ultra2/160/U320 LVD Cable (VHDCI68 to HD68 M/M), 3 ft. (0.91 m)

MODEL NUMBER: **S455-003**



Highlights

- Short length cable for Server to i.e., Tape Loader Storage
- Premium double-shielded cable
- Meets the most current SCSI specifications for high-speed devices

System Requirements

- Any external SCSI device or host controller card requiring VHDCI68 or HD68 interface

Package Includes

- 3-ft. (0.91 m) SCSI U320/U160 LVD/SE cable, VHDCI68M to HD68M

Description

Moving your network into the next phase of SCSI solutions? Look no further than these SCSI U320/U160 cables. Supports all legacy transfer rates including Ultra 320. Multi-platform SCSI III external peripheral cable, VHDCI68M/HD68M. This cable is designed to connect two SCSI III (fast and wide) or SCSI II devices together. Manufactured using double-shielded 34 twisted-pair high-impedance cable. Constructed with low-capacitance, impedance matched, 28 AWG, stranded, tinned copper cable with insulated in polypropylene.

Features

- Supports all SCSI transfer rates through 320Mbps
- LVD/SE compliant
- Backwards compatibility with previous SCSI generations
- Double shielded (foil and braid)
- All SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Check out a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest Ultra 320 to legacy SCSI-1 and every combination in between

Specifications

OVERVIEW	
UPC Code	037332138187
Technology	SCSI
CONNECTIONS	
Side A - Connector 1	VHDCI68 (MALE)
Side B - Connector 1	HD68 (MALE)



Powering Business Worldwide



PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	0.50 x 6.00 x 6.00
Shipping Dimensions (hwd / cm)	1.27 x 15.24 x 15.24
Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.