

Internal SAS Cable, 4-in-1 32Pin (SFF-8484) to 32Pin (SFF-8484) Cable, 1M (3-ft.)

MODEL NUMBER: **S500-01M**



Highlights

- 32-pin SFF-8484 to SFF-8484 Internal SAS Cable
- Supports data rates up to 6.0Gbs
- Straight backshell configuration

System Requirements

- SAS Host Bus Adapter and Backplane with SFF-8484 mating connector

Package Includes

- 1-Meter Internal SAS 4-in-1 SFF-8484 to SFF-8484 Cable

Description

Tripp Lite's 32-pin SFF-8484 to SFF-8484 Internal SAS (Serial Attached SCSI) cable is ideal for use with SAS controllers to SAS disk drive back planes. High-performance cable provides differential pair signaling with less than 5ps/m in pair skew, improved EMI protection, and 3.0Gbs data rate with rates up to 6.0Gbs. Thinner, flexible cable enables more efficient routing, with improved airflow and thermal mechanics. Configuration of storage devices is simplified. Tripp Lite's SAS assemblies are RoHS compliant and feature a

Features

- Internal SAS 4-in-1 SFF-8484 to SFF-8484 Cable - 1 meter
- Supports data rates of up to 6.0Gbs
- Thin, flexible cable for easy routing and increased airflow
- RoHS compliant

Specifications

OVERVIEW	
UPC Code	037332138132
CONNECTIONS	
Side A - Connector 1	SFF-8484
Side B - Connector 1	SFF-8484
PHYSICAL	
Color	Black
Cable Length (ft.)	3



Powering Business Worldwide



Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.35
Shipping Weight (kg)	0.16
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.