

Internal SAS Cable, 4-in-1 32Pin (SFF-8484) to 4 x 7pin Cable, 1M (3.28 ft.)

MODEL NUMBER: **S502-01M**



Highlights

- 32-pin SFF-8484 to 4 x 7-pin internal SAS cable
- Supports data rates of up to 6.0Gbs
- Straight backshell configuration
- 1 meter in length

System Requirements

- SAS Host Bus Adapter and Backplane with SFF-8484 mating connector

Package Includes

- 1-Meter Internal SAS 4-in-1 SFF-8484 to 4 x 7pin Cable

Features

- SFF-8484 to 4 x 7pin SAS Cable - 1 meter
- Supports data rates up to 6.0Gbs
- Thin, flexible cable for easy routing and increased airflow
- RoHS Compliant

Specifications

OVERVIEW	
UPC Code	037332138125
Technology	SAS; Ribbon/Internal
CONNECTIONS	
Side A - Connector 1	SFF-8484
Side B - Connector 1	7 PIN SATA (MALE)
PHYSICAL	
Color	Red
Cable Jacket Color	Red
Cable Length (ft.)	3.3
Cable Length (m)	1.01
Shipping Dimensions (hwd / in.)	0.25 x 4.40 x 5.00
Shipping Dimensions (hwd / cm)	0.64 x 11.18 x 12.70



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.