

## Internal SAS Cable, 4-Lane mini-SAS (SFF-8087) to 4xSatA 7pin, 3 ft. (0.91 m)

MODEL NUMBER: **S508-003**



### Highlights

- Positive and passive latching ensures that the plug remains mated to receptacle
- All internal Mini-SAS assemblies are capable of supporting SAS/SATA generation I, II, and III bandwidths ( up to 6Gbps )
- Reduced mechanical size offers up to 4 times the port density of the current x4 solution

### Package Includes

- 3 ft. Internal SAS Cable, SFF-8087 to 4 x 7pin SATA

### Features

- Positive and passive latching ensures that the plug remains mated to receptacle
- All internal mini SAS assemblies are capable of supporting SAS/SATA generation I, II, and III bandwidths ( up to 6Gbps )
- Reduced mechanical size offers up to 4 times the port density of the current x4 solution
- For Controller to hard drive applications

## Specifications

OVERVIEW	
UPC Code	037332143341
Technology	SAS; SATA/eSATA; Ribbon/Internal
INPUT	
Cable Length (ft.)	3
Cable Length (m)	0.9
PHYSICAL	
Color	Red
Shipping Dimensions (hwd / cm)	1.27 x 2.54 x 20.07
Shipping Dimensions (hwd / in.)	0.50 x 1.00 x 7.90
Shipping Weight (kg)	0.09



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Shipping Weight (lbs.)	0.20
<b>CONNECTIONS</b>	
Side A - Connector 1	SFF-8087
Side B - Connector 1	7 PIN SATA (MALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>