

External SAS Cable, 4 Lane - mini-SAS (SFF-8088) to mini-SAS (SFF-8088), 3M (9.84 ft.), TAA

MODEL NUMBER: **S524-03M**



Features

- 3-meter External SAS Cable, SFF-8088 to SFF-8088
- Made with High-Performance Infiniband Cable
- Support data rates from 3.0 up to 6.0 gigabytes per second
- SFF-8088 connectors in diecast zinc housing for durability
- RoHS compliant
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332152008
Technology	SAS
INPUT	
Cable Length (ft.)	9.8
Cable Length (m)	3
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	22.91 x 17.81 x 1.27
Shipping Dimensions (hwd / in.)	9.02 x 7.01 x 0.50

Highlights

- High-performance 3-meter SAS external cable
- Mini-SAS SFF-8088 (iSAS) to Mini-SAS SFF-8088 (iSAS)
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- SAS Controllers, SAS Chassis, SAS/SATA Hard Drives

Package Includes

- 3-Meter SAS External, SFF-8088 to SFF-8088 Cable



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (kg)	0.28
Shipping Weight (lbs.)	0.61
CONNECTIONS	
Side A - Connector 1	SFF-8088
Side B - Connector 1	SFF-8088
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>