

Mini-SAS External HD Cable - SFF-8644 to SFF-8644, 12 Gbps, 1 m (3.3 ft.)

MODEL NUMBER: **S528-01M**



High-performance mini-SAS external HD cable connects two storage devices with external SFF-8644 connectors.

Features

High-Performance Mini-SAS External HD Cable for Connecting SAN Devices This four-channel InfiniBand cable connects two storage devices with external mini-SAS HD SFF-8644 connectors, such as 12G RAID controllers, SATA hard drives, enclosures and JBOD devices. It supports data transfer rates up to 12 Gbps, which is faster than eSATA, USB 3.0 and Thunderbolt cables. The high-density connectors are surrounded by durable die-cast zinc that is compatible with shielded external connectors. Protective caps defend the connectors against dust and damage. Convenient pull-tabs make it easy to disconnect the cable in crowded racks and other applications. The S528-01M is backward compatible with previous SAS versions to ensure compatibility with your devices.

Specifications

Highlights

- Ideal for connecting storage area network (SAN) devices or hard drives
- Protective caps over die-cast zinc housings shield ends from dust and damage
- Convenient pull tabs make it easier to disconnect cable in crowded racks
- Supports data transfer speeds up to 12 Gbps—faster than eSATA, USB 3.0 and Thunderbolt
- Backward compatible with previous SAS versions for sure compatibility with your device

Applications

- Connect two high-performance JBOD storage devices for the purpose of consolidating and sharing data in a small-to-medium company or organization

System Requirements

- Works with SAN devices, SAS/SATA hard drives and other SAS interface devices with SFF-8644 external connectors

Package Includes

- S528-01M Mini-SAS External HD Cable - SFF-8644 to SFF-8644, 1 m



OVERVIEW	
UPC Code	037332222305
INPUT	
Cable Length (ft.)	3.28
Cable Length (m)	1
PHYSICAL	
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	32 ~ 104F (0 ~ 40C)
Storage Temperature Range	-4 ~ 149F (-20 ~ 65C)
Operating Humidity Range	20 ~ 80%
Storage Humidity Range	10 ~ 90%
CONNECTIONS	
Side A - Connector 1	SFF-8644
Side B - Connector 1	SFF-8644
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
Technology	SAS
STANDARDS & COMPLIANCE	
Certifications	RoHS Certified
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>