



# Surge Suppressor- State of the art protection for every application

MODEL NUMBER: S6-DLX



#### **Highlights**

- 6 outlets/6 ft. cord
- 1050 joule rating
- Modem/fax surge protection
- \$15,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

#### **Package Includes**

- S6-DLX Surge Suppressor
- Telephone cord
- · Child Safety Covers
- · Color-coded cord identifiers
- Warranty information with instruction manual

### **Description**

The S6-DLX Surge Suppressor from Tripp Lite has 6 outlets and a 6-ft. cord with a space-saving right-angle plug. The unit has 1,050 joules of surge energy absorption to handle the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. A telephone cord is also included. Diagnostic LEDs alert the user to potential power problems. \$15,000 Ultimate Lifetime Insurance (USA & Canada Only). No warranty cards required for coverage! The Super 6 Deluxe comes with child safety covers and color-coded cord identifiers.

#### **Features**

- · 6 outlets with child safety covers
- 6-ft. cord with space-saving right-angle plug
- Built-in RJ11 jacks prevent surges from damaging your modem / fax / phone equipment; 6-ft. telephone cord included
- \$15,000 Ultimate Lifetime Insurance (USA & Canada Only) covers connected equipment No warranty cards required for coverage!
- Surge energy absorption: 1,050 joules; 42,500 amps
- 15 amp circuit breaker
- 2 diagnostic LEDs indicate AC present & line fault
- EMI/RFI noise filtering
- Keyhole supports for wall mounting
- Color-coded cord identifiers
- Lifetime product warranty

## **Specifications**

INPUT	
Nominal Input Voltage(s) Supported	100V AC
Recommended Electrical Service	120V (110-125V)





Voltage Compatibility (VAC)	120	
Input Plug Type	NEMA 5-15P	
Input Cord Length (ft.)	6	
Right-Angle Plug	Yes	
Input Cord Length (m)	1.83	
Integrated Cord Clip	No	
ОИТРИТ		
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(6) 5-15R	
Circuit Breaker (amps)	15	
Transformer Accommodation	(2) Yes	
USER INTERFACE, ALERTS & CONTROLS		
Diagnostic LED(s)	Yes	
Switches	Two position on/off power switch	
Diagnostic LED Details	PROTECTION PRESENT, LINE OK	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	1050	
AC Suppression Response Time	< 1 ns	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression	
AC Suppression Surge Current Rating	42,500 amps	
UL1449 Let Through Rating	330V - UL Verified	
EMI / RFI Filtering	Yes	
Immunity	Conforms to IEE 587 / ANSI C62.41	
Automatic Shut-Off	No	
DATALINE SURGE SUPPRESSION		
Telephone/DSL Protection Details	1 line	
Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	
Telephone/DSL Protection	Yes	
PHYSICAL		
Color	Light Gray	
Material of Construction	Plastic	





Power Cord Color	Light Gray	
Housing Color	Light Gray	
Mounting Holes or Slots	Yes	
Receptacle Color	Light gray	
Unit Dimensions (hwd / in.)	1.250 x 3.250 x 8.250	
Unit Dimensions (hwd / cm)	3.2 x 8.3 x 21	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$15,000 <a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.