

Power It! 1-Outlet Universal Travel Charger and Power Strip - 5-15R Outlet, USB-C and USB-A Ports, 32W PD Charging, 5-15P Direct Plug-In, Gray

MODEL NUMBER: SK10C32



Travel charger with PD charging powers your laptop in a hotel or airport while also charging your tablet and smartphone.

Features

1-Outlet Power Strip with USB Charging Keeps Your Devices Powered and Ready

Ideal for travel use in a hotel, airport or library, as well as your home, office, retail or industrial workstation, this Power It!® power strip/charger has a single NEMA 5-15R outlet for powering a wide range of electronic devices, including laptops and notebook computers. One USB-A port and one USB-C port share 3.4A and 32W Power Delivery (PD) charging for your smartphone, tablet and other mobile devices. All three ports can be used at the same time. The unit plugs directly into a wall outlet, avoiding annoying cord clutter.

Specifications

OVERVIEW	
UPC Code	037332288813
Product Type	Power Strip
Charging Form Factor	Direct Plug-In
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120

Highlights

- NEMA 5-15R outlet distributes AC power to connected home/office/work equipment
- Plugs directly into the wall (no cord required) for easy installation and no cable clutter
- USB-A and USB-C ports power and charge smartphones and other mobile devices
- Compact power strip fits snugly into backpack or laptop bag for convenient travel use

Package Includes

- SK10C32 1-Outlet Universal Travel Charger, Gray
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1875
Output Receptacles	5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	No
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
CHARGING	
Number of Charging Ports	2
Total Charging Amps	1 USB-A and 1 USB-C
Charging Method	USB
Charging Port Type	USB A (FEMALE); (1) USB C (FEMALE)
Charging Ports / Amps	(2) 3.4A
Overcharge Protection	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	0
EMI / RFI Filtering	no
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Color	Gray
Material of Construction	Plastic



Powering Business Worldwide

TRIPP LITE
SERIES

Housing Color	Gray
Mounting Holes or Slots	No
Receptacle Color	Gray
Shipping Dimensions (hwd / in.)	3.20 x 1.96 x 3.12
Shipping Dimensions (hwd / cm)	8.13 x 4.98 x 7.92
Shipping Weight (lbs.)	0.26
Shipping Weight (kg)	0.12
Unit Dimensions (hwd / in.)	3.000 x 1.640 x 2.480
Unit Weight (lbs.)	0.22
Unit Weight (kg)	0.10
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
Built-In Circuit Breaker	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 498
Product Compliance	RoHS; RoHS3; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.