

Protect It! 3-Outlet Surge Protector, Direct Plug-In, 540 Joules, 2.1A USB Charger

MODEL NUMBER: SK120USB



Highlights

- 3 outlets/direct plug-in
- 540 joule rating
- 2.1 amp USB charging
- Fold down plug
- Carrying pouch
- Diagnostic LED

Package Includes

- SK120USB surge suppressor
- Carrying pouch

Description

The SK120USB surge suppressor offers reliable surge and line noise protection. The compact direct plug-in design allows for easy portability with fold down plug and carrying pouch and features 3 outlets, 1 in front and 1 on each side of unit and 540 joules of surge energy absorption. The diagnostic LED alerts you to potential wiring or protection faults before connected equipment is damaged. 2.1 amp USB charging ports offer fast charging for smartphones, tablets, MP3 players and other portable devices. \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 3 outlets / direct plug-in - 1 on face of product and 1 on each side
- Surge suppression rating: 540 joules
- 2.1 amp USB Charger
- Fold down plug
- Carrying pouch
- EMI/RFI noise filtering
- Diagnostic LED indicates Protected (green)
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW	
UPC Code	037332180360
Product Type	Surge Protector



Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(3) 5-15R
Circuit Breaker (amps)	15
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	540
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
Clamping Voltage (RMS)	500
AC Suppression Surge Current Rating	27,000
UL1449 Let Through Rating	500, 400, 500
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	No
CHARGING	
Charging Ports / Amps	(2) 2.1A



Number of Charging Ports	2
Charging Method	USB
Charging Port Type	USB A (FEMALE)
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Antimicrobial Coating	No
Color	Black
Housing Color	Black
Integrated Keyhole Mounting Slots	No
Material of Construction	Plastic
Receptacle Color	Gray
Shipping Dimensions (hwd / cm)	11.68 x 7.11 x 6.10
Shipping Dimensions (hwd / in.)	4.60 x 2.80 x 2.40
Shipping Weight (kg)	0.20
Shipping Weight (lbs.)	0.44
Unit Dimensions (hwd / cm)	10.9 x 5.69 x 3.51
Unit Dimensions (hwd / in.)	4.29 x 2.24 x 1.38
Unit Weight (kg)	0.14
Unit Weight (lbs.)	.31
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Approvals	RoHS
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$5,000 Ultimate Lifetime Insurance



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>