

TAA-Compliant Protect It! 3-Outlet Surge Protector, Direct Plug-In, 540 Joules, 2.1A USB Charger

MODEL NUMBER: SK120USBTAA



Highlights

- Compliant with the Federal Trade Agreement Act (TAA) for GSA schedule purchases
- 3 outlets/direct plug-in
- 540 joule rating
- 2.1 amp USB charging
- Fold down plug
- Carrying pouch
- Diagnostic LED
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Package Includes

- SK120USBTAA surge suppressor
- Carrying pouch

Description

The SK120USBTAA surge suppressor offers reliable surge and line noise protection. The compact direct plug-in design allows for easy portability with fold down plug and carrying pouch and features 3 outlets, 1 in front and 1 on each side of unit and 540 joules of surge energy absorption. The diagnostic LED alerts you to potential wiring or protection faults before connected equipment is damaged. 2.1 amp USB charging ports offer fast charging for smartphones, tablets, MP3 players and other portable devices. \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- Compliant with the Federal Trade Agreement Act (TAA) for GSA schedule purchases
- 3 outlets / direct plug-in - 1 on face of product and 1 on each side
- Surge suppression rating: 540 joules
- 2.1 amp USB Charger
- Fold down plug
- Carrying pouch
- EMI/RFI noise filtering
- Diagnostic LED indicates Protected (green)
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW	
UPC Code	037332183415
INPUT	



Powering Business Worldwide



Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(3) 5-15R
Circuit Breaker (amps)	15
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
CHARGING	
Number of Charging Ports	2
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(2) 2.1A
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	540
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
AC Suppression Surge Current Rating	27,000
UL1449 Let Through Rating	500, 400, 500
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No



Powering Business Worldwide



Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Color	Black
Material of Construction	Plastic
Mounting Holes or Slots	No
Receptacle Color	Gray
Shipping Dimensions (hwd / in.)	25.40 x 4.60 x 2.60
Shipping Dimensions (hwd / cm)	64.52 x 11.68 x 6.60
Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
Unit Dimensions (hwd / in.)	4.290 x 2.240 x 1.380
Unit Dimensions (hwd / cm)	10.9 x 5.69 x 3.51
Unit Weight (lbs.)	.31
Unit Weight (kg)	0.14
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$5,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.