

Safe-IT 2-Outlet Universal Travel Charger - 5-15R Outlets, 2 USB Ports, Direct Plug-In with 5 Plug Options, Antimicrobial Protection

MODEL NUMBER: SK2UTRAVAM



Travel charger powers and charges up to 4 devices, including phones and tablets, while working at home, hotel or open office.

Features

2-Outlet 2-Port Travel Charger Keeps Your Devices Powered and Ready

Ideal for your home or office workstation or travel use, this Safe-IT™ power strip charger accepts a wide range of electronic devices. Plug your printer, external hard drive or other home/office electronics into two NEMA 5-15R outlets. Two USB-A ports share 3.4A for charging your smartphone, tablet and other mobile devices.

Direct Plug-In Design Makes It Easy to Work from Anywhere

The SK2UTRAVAM plugs directly into a wall outlet with no messy cables needed. It comes with five international plug adapters (North America, Japan, United Kingdom, Europe, China), so you can travel with the power strip charger and use it almost anywhere in the world. A black carrying pouch is included to keep the charger safe inside your suitcase, backpack, purse or laptop bag.

Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Work Environment

The Safe-IT SK2UTRAVAM features antimicrobial protection that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

Specifications

OVERVIEW	
UPC Code	037332265760
Product Type	Power Strip
Charging Form Factor	Direct Plug-In
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	

Highlights

- 2 NEMA 5-15R outlets distribute AC power to connected home/office equipment
- 2 USB ports share 3.4A for fast charging of phones, tablets and other mobile devices
- Convenient direct plug-in charger includes 5 international plug adapters
- Compact power strip fits snugly in backpack or purse for expedient portability
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

Package Includes

- SK2UTRAVAM 2-Outlet Universal Travel Charger
- (5) International plug adapters (North America, Japan, U.K., Europe, China)
- Carrying pouch, black
- Owner's manual



Powering Business Worldwide



Nominal Input Voltage(s) Supported	110V AC; 240V AC
Recommended Electrical Service	120V
Input Cord Length Details	Direct Plug-In
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(2) 5-15R
Circuit Breaker (amps)	10
Transformer Accommodation	No
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
CHARGING	
Number of Charging Ports	2
Total Charging Watts	17
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(2) 3.4A
Overcharge Protection	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	0
EMI / RFI Filtering	no
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	



Powering Business Worldwide



Color	Black
Material of Construction	Plastic
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
Unit Dimensions (hwd / in.)	3.500 x 2.800 x 1.300
Unit Dimensions (hwd / cm)	8.89 x 7.11 x 3.30
Unit Weight (lbs.)	0.26
Unit Weight (kg)	0.12
Input Cord Color	Black
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	Yes
Built-In Circuit Breaker	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 60950-1 (Canada)
Product Compliance	RoHS; RoHS3; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.