

Protect It! 3-Outlet Surge Protector, Direct Plug-In, 660 Joules, 2 Diagnostic LEDs

MODEL NUMBER: SK3-0



Highlights

- 3 outlets/direct plug-in
- 660 joule rating
- Diagnostic LEDs

Package Includes

- SK3-0 surge suppressor

Description

The SK3-0 surge suppressor offers reliable surge and line noise protection. The compact direct plug-in design allows for easy portability and features 3 outlets and 660 joules of surge energy absorption. Diagnostic LEDs alert you to potential wiring or protection faults before connected equipment is damaged. \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 3 outlets / direct plug-in
- Surge suppression rating: 660 joules
- EMI/RFI noise filtering
- Diagnostic LEDs indicate Protected (green) & Grounded (red)
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332166319
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V



Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
Maximum Surge Amps	39000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(3) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	660
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
Clamping Voltage (RMS)	150
AC Suppression Surge Current Rating	27,000
UL1449 Let Through Rating	500, 400, 500
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Antimicrobial Coating	No
Color	Light Gray
Housing Color	Light Gray
Integrated Keyhole Mounting Slots	No
Material of Construction	Plastic
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	14.99 x 7.62 x 6.86
Shipping Dimensions (hwd / in.)	5.90 x 3.00 x 2.70
Shipping Weight (kg)	0.15
Shipping Weight (lbs.)	0.32
Unit Dimensions (hwd / cm)	6.35 x 9.7 x 5.33
Unit Dimensions (hwd / in.)	2.5 x 3.8 x 2.1
Unit Weight (kg)	0.09
Unit Weight (lbs.)	.20
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Approvals	RoHS
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$5,000 Ultimate Lifetime Insurance

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>