

## Protect It! 3-Outlet Surge Protector, Direct Plug-In, 540 Joules, 2.1 A USB Charger, Diagnostic LED

MODEL NUMBER: SK30USB



### Highlights

- 3 outlets/direct plug-in
- 540 joule rating
- 2.1 amp USB charging
- Diagnostic LED

### Package Includes

- SK30USB surge suppressor

### Description

The SK30USB surge suppressor offers reliable surge and line noise protection. The compact direct plug-in design allows for easy portability and features 3 outlets and 540 joules of surge energy absorption. Diagnostic LED alerts you to potential wiring or protection faults before connected equipment is damaged. 2.1 amp USB charging ports offer fast charging for smartphones, tablets, MP3 players and other portable devices. \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

### Features

- 3 outlets / direct plug-in
- Surge suppression rating: 540 joules
- 2.1 amp USB Charger
- EMI/RFI noise filtering
- Diagnostic LED indicates Protected (green)
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

## Specifications

| OVERVIEW             |                              |
|----------------------|------------------------------|
| UPC Code             | 037332180353                 |
| Product Type         | Surge Protector              |
| Charging Form Factor | Strip                        |
| Device Compatibility | Phone; Tablet; Amazon Kindle |

| <b>INPUT</b>                                 |  |
|--|--|
| Nominal Input Voltage(s) Supported           | 120V AC  |
| Recommended Electrical Service               | 120V   |
| Input Cord Length Details                    | Direct Plug-In   |
| Voltage Compatibility (VAC)                  | 120  |
| Input Plug Type                              | NEMA 5-15P   |
| Input Cord Length (ft.)                      | 0  |
| Right-Angle Plug                             | No   |
| Input Cord Length (m)                        | 0.00   |
| Integrated Cord Clip                         | No   |
| <b>OUTPUT</b>                                |  |
| Frequency Compatibility                      | 60 Hz  |
| Output Receptacles                           | (3) 5-15R  |
| Circuit Breaker (amps)                       | 15   |
| Transformer Accommodation                    | (2) Yes  |
| Right-Angle Outlets                          | No   |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |  |
| Diagnostic LED(s)                            | Yes  |
| <b>CHARGING</b>                              |  |
| Number of Charging Ports                     | 2  |
| Total Charging Watts                         | 10.5   |
| Charging Method                              | USB  |
| Charging Port Type                           | USB A (FEMALE)   |
| Charging Ports / Amps                        | (2) 2.1A   |
| Overcharge Protection                        | No   |
| <b>SURGE / NOISE SUPPRESSION</b>             |  |
| AC Suppression Joule Rating                  | 540  |
| AC Suppression Response Time                 | < 1ns  |
| Protection Modes                             | Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression |
| AC Suppression Surge Current Rating          | 27,000   |
| UL1449 Let Through Rating                    | 500, 400, 500  |
| EMI / RFI Filtering                          | Yes  |

|  |   |
|--|---|
| Immunity   | Conforms to IEE 587/ANSI C62.41   |
| Automatic Shut-Off   | Yes   |
| <b>DATALINE SURGE SUPPRESSION</b>                          |   |
| Cable (Coax) Protection                                    | No  |
| Network (Ethernet) Protection                              | No  |
| Telephone/DSL Protection                                   | No  |
| <b>PHYSICAL</b>  |   |
| Material of Construction                                   | Plastic   |
| Power Cord Color   | Black   |
| Mounting Holes or Slots                                    | No  |
| Receptacle Color   | Black   |
| Shipping Dimensions (hwd / in.)                            | 6.30 x 2.70 x 4.00  |
| Shipping Dimensions (hwd / cm)                             | 16.00 x 6.86 x 10.16  |
| Shipping Weight (lbs.)                                     | 0.60  |
| Shipping Weight (kg)                                       | 0.27  |
| Unit Dimensions (hwd / in.)                                | 5.280 x 3.740 x 1.180   |
| Unit Dimensions (hwd / cm)                                 | 13.40 x 9.50 x 3.00   |
| Unit Weight (lbs.)   | 0.41  |
| Unit Weight (kg)   | 0.19  |
| Input Cord Color   | Black   |
| <b>FEATURES &amp; SPECIFICATIONS</b>                       |   |
| Antimicrobial  | No  |
| Rotatable Outlets  | No  |
| GaN Technology   | No  |
| <b>STANDARDS &amp; COMPLIANCE</b>                          |   |
| Product Certifications                                     | CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 42 (Canada); NOM (Mexico); UL 1449; UL 497A                                 |
| Product Compliance   | RoHS  |
| <b>WARRANTY &amp; SUPPORT</b>                              |   |
| Product Warranty Period (Worldwide)                        | Lifetime limited warranty   |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$5,000&nbsp;<a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>&nbsp; |



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2022 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.