

Protect It! Personal Charging Station with 3-Outlet Surge Protector, Direct Plug-In, 540 Joules, 4 USB Ports, 3 AC Outlets

MODEL NUMBER: SK34USBB



Provides reliable surge protection, charging, performance enhancement and convenient storage for mobile devices, such as tablets, MP3 players and smartphones. Ideal for home, office, workstations and hotel rooms.

Description

The SK34USBB Protect It! Personal Charging Station charges your sensitive electronics and protects them against surges, power fluctuations and EMI/RFI line noise that can damage devices and destroy data. Ideal for home, office, workstations, dorm rooms and hotel rooms, the SK34USBB features 540 joules of surge protection. Because of its small size and direct plug-in design, you can take it anywhere. With three NEMA 5-15R AC outlets and four USB ports with 4.8 total amps, the SK34USBB can charge multiple power-hungry devices, such as tablets, MP3 players and smartphones. A built-in top slot and an additional slide-out slot hold your devices to keep them safe and organized and avoid cable clutter. A diagnostic LED confirms protection status at a glance. An automatic shutoff feature permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required. Backed by \$10,000 of Ultimate Lifetime Insurance in the U.S., Canada and Puerto Rico only.

Features

Charges and Protects Your Portable Devices Charges mobile devices, such as tablets, MP3 players and smartphones
Ideal for home, office, workstations, dorm rooms and hotel rooms
540 joules protect against surges, power fluctuations and EMI/RFI line noise
Diagnostic LED confirms protection status at a glance
Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required
Direct plug-in design for easy transport anywhere

Easily Handles Multiple Devices 3 NEMA 5-15R outlets 4 USB charging ports (4.8A total)

Stores Mobile Devices While Charging Built-in top slot and additional pull-out slot hold 2 devices
Keeps devices safe and organized
Cuts down on cable clutter

Specifications

Highlights

- 3 NEMA 5-15R outlets
- 4 USB charging ports (4.8A total)
- 2 slots for holding tablets and smartphones
- 540 joules of surge protection

Package Includes

- SK34USBB Protect It! Personal Charging Station w/ 3-Outlet Surge Protector
- Owner's manual



OVERVIEW	
UPC Code	037332195319
Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Plug Features	Right Angle (36D)
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(3) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
CHARGING	
Number of Charging Ports	4
Total Charging Watts	24
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(4) 4.8A
Overcharge Protection	No



SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	540
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	600, 700, 700
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	7.11 x 10.41 x 14.22
Shipping Dimensions (hwd / in.)	2.80 x 4.10 x 5.60
Shipping Weight (kg)	0.32
Shipping Weight (lbs.)	0.70
Unit Dimensions (hwd / in.)	4.96 x 3.70 x 1.32
Unit Dimensions (hwd / cm)	12.6 x 9.5 x 3.35
Unit Weight (lbs.)	0.57
Unit Weight (kg)	0.26
Input Cord Color	Black
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Rotatable Outlets	No
GaN Technology	No
STANDARDS & COMPLIANCE	



Approvals	RoHS
UL1449 3rd Edition (AC Suppression)	UL498A:2008 (2nd Ed); UL1449:2014 (4th Ed), CAN/CSA-C22.2 No. 269.3:2017 (2nd Ed)
NOM (Mexico)	NOM
UL497A (Communications)	No
Industry Canada (Communications)	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>