

Protect It! 6-Outlet Surge Protector - 5-15R Outlets, 5-15P Direct Plug-In, 490 Joules, Black

MODEL NUMBER: SK62SL



Protects your computer and other home/office electronics against dangerous power surges, spikes and line noise.

Features

6-Outlet Surge Protector Safeguards Your Sensitive Electronics

Ideal for your home, office, retail or industrial workstation, this Protect It!® surge protector features a surge suppression rating of 490 joules to defend your valuable electronic components against power surges and spikes. The unit plugs directly into a wall outlet, avoiding annoying cord clutter.

NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your computer, printer, wireless router, desk lamp, game console and other home/office electronics into six NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

This surge protector filters out disruptive EMI (electromagnetic interference) and RFI (radio frequency interference) line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Includes the Latest Safety Features to Maintain Your Equipment's Well-Being

An integrated 15A circuit breaker provides overload protection for connected devices. A bright green diagnostic LED located in the middle of the unit confirms at a glance that your equipment is protected.

Highlights

- 6 NEMA 5-15R outlets distribute AC power to connected home/office/work equipment
- 490 joules protect your valuable electronics against dangerous surges and spikes
- Plugs directly into the wall (no cord required) for easy installation and no cable clutter
- Bright green diagnostic LED lets you know at a glance that your equipment is protected

Package Includes

- SK62SL 6-Outlet Surge Protector, Black
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332294487
Product Type	Surge Protector
Charging Form Factor	Direct Plug-In
Device Compatibility	Phone; Tablet; Amazon Kindle



Powering Business Worldwide

TRIPP LITE
SERIES

INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1875
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(4) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Green - Protected
CHARGING	
Overcharge Protection	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	490
AC Suppression Response Time	< 1 ns
Protection Modes	L-N line suppression
UL1449 Let Through Rating	600
EMI / RFI Filtering	150KHz-100MHz
Isolated Filter Banks	no
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	



Powering Business Worldwide

TRIPP LITE
SERIES

Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Housing Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	7.30 x 3.80 x 2.90
Shipping Dimensions (hwd / cm)	18.54 x 9.65 x 7.37
Shipping Weight (lbs.)	0.73
Shipping Weight (kg)	0.33
Unit Dimensions (hwd / in.)	5.600 x 3.600 x 2.800
Unit Dimensions (hwd / cm)	14.2 x 9.1 x 7.1
Unit Weight (lbs.)	0.57
Unit Weight (kg)	0.26
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 104°F (-15° to 40°C)
Operating Humidity Range	20% to 85% RH
Storage Humidity Range	0% to 90% RH
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 42 (Canada); UL 1449
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 Ultimate Lifetime Insurance



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.