

# Protect It! 6-Outlet Surge Protector - 5-15R Outlets, 2 USB Ports, 5-15P Direct Plug-In, 490 Joules, Black

MODEL NUMBER: SK62USBC



Protects your computer and other home/office electronics against dangerous power surges, spikes and line noise.

## Features

### 6-Outlet Surge Protector with USB Charging Safeguards Your Sensitive Electronics

Ideal for your home, office, retail or industrial workstation, this Protect It!® surge protector features a surge protection rating of 490 joules to defend your valuable electronic components against power surges and spikes. The unit plugs directly into a wall outlet, avoiding annoying cord clutter.

### NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your computer, printer, wireless router, desk lamp and other home/office electronics into six NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise.

### Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

This surge protector filters out disruptive EMI (electromagnetic interference) and RFI (radio frequency interference) line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

### USB Charger Keeps Mobile Devices Ready for Use

One USB-C port and one USB-A port are available for charging your smartphone, tablet or other USB mobile devices. They share 4A for charging multiple devices at the same time.

### Includes the Latest Safety Features to Maintain Your Equipment's Well-Being

An integrated 15A circuit breaker provides overload protection for connected devices. A green LED confirms at a glance that your equipment is protected.

## Highlights

- 6 NEMA 5-15R outlets distribute AC power to connected home/office/work equipment
- 490 joules protect your valuable electronics against dangerous surges and spikes
- Plugs directly into the wall (no cord required) for easy installation and no cable clutter
- USB ports share 4A for fast charging of phones and other mobile devices
- Easy-to-see green LED lets you know at a glance that your equipment is protected

## Package Includes

- SK62USBC 6-Outlet Surge Protector, Black
- Owner's manual

## Specifications

| OVERVIEW     |                 |
|--------------|-----------------|
| UPC Code     | 037332283450    |
| Product Type | Surge Protector |



Powering Business Worldwide



|  |                                |
|--|--------------------------------|
| Charging Form Factor                         | Direct Plug-In                 |
| Device Compatibility                         | Phone; Tablet; Amazon Kindle   |
| <b>INPUT</b>                                 |                                |
| Nominal Input Voltage(s) Supported           | 120V AC                        |
| Recommended Electrical Service               | 120V                           |
| Input Cord Length Details                    | Direct Plug-In                 |
| Voltage Compatibility (VAC)                  | 120                            |
| Input Plug Type                              | NEMA 5-15P                     |
| Input Cord Length (ft.)                      | 0                              |
| Right-Angle Plug                             | No                             |
| Input Cord Length (m)                        | 0.00                           |
| Integrated Cord Clip                         | No                             |
| <b>OUTPUT</b>                                |                                |
| Frequency Compatibility                      | 60 Hz                          |
| Output Receptacles                           | (6) 5-15R                      |
| Circuit Breaker (amps)                       | 15                             |
| Transformer Accommodation                    | (4) Yes                        |
| Right-Angle Outlets                          | No                             |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |                                |
| Diagnostic LED(s)                            | Yes                            |
| Diagnostic LED Details                       | Green - Protected              |
| <b>CHARGING</b>                              |                                |
| Number of Charging Ports                     | 2                              |
| Total Charging Amps                          | 4                              |
| Total Charging Watts                         | 1875                           |
| Charging Method                              | USB                            |
| Charging Port Type                           | USB A (FEMALE); USB C (FEMALE) |
| Charging Ports / Amps                        | (2) 2A                         |
| Overcharge Protection                        | No                             |
| Charging Amps per Port                       | 2A                             |
| <b>SURGE / NOISE SUPPRESSION</b>             |                                |
| AC Suppression Joule Rating                  | 490                            |
| AC Suppression Response Time                 | < 1 ns                         |



Powering Business Worldwide



|                                      |  |
|--------------------------------------|--|
| Protection Modes                     | L-N line suppression   |
| UL1449 Let Through Rating            | 600  |
| EMI / RFI Filtering                  | 150KHz-100MHz  |
| Isolated Filter Banks                | no   |
| Immunity                             | Conforms to IEE 587/ANSI C62.41  |
| Automatic Shut-Off                   | No   |
| <b>DATALINE SURGE SUPPRESSION</b>    |  |
| Cable (Coax) Protection              | No   |
| Network (Ethernet) Protection        | No   |
| Telephone/DSL Protection             | No   |
| <b>PHYSICAL</b>                      |  |
| Material of Construction             | Plastic  |
| Housing Color                        | Black  |
| Mounting Holes or Slots              | No   |
| Receptacle Color                     | Black  |
| Shipping Dimensions (hwd / in.)      | 7.30 x 3.80 x 2.90   |
| Shipping Dimensions (hwd / cm)       | 18.54 x 9.65 x 7.37  |
| Shipping Weight (lbs.)               | 0.73   |
| Shipping Weight (kg)                 | 0.33   |
| Unit Dimensions (hwd / in.)          | 5.600 x 3.600 x 2.800  |
| Unit Dimensions (hwd / cm)           | 14.2 x 9.1 x 7.1   |
| Unit Weight (lbs.)                   | 0.57   |
| Unit Weight (kg)                     | 0.26   |
| <b>FEATURES &amp; SPECIFICATIONS</b> |  |
| Rotatable Outlets                    | No   |
| Antimicrobial                        | No   |
| GaN Technology                       | No   |
| <b>STANDARDS &amp; COMPLIANCE</b>    |  |
| Product Certifications               | CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 42 (Canada); UL 1449 |
| Product Compliance                   | FCC Part 15 Class B (USA); RoHS  |
| <b>WARRANTY &amp; SUPPORT</b>        |  |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty  |



Powering Business Worldwide



|   |  |
|---|--|
| Connected Equipment Insurance<br>(U.S., Canada & Puerto Rico) | \$20,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime<br>Insurance</a> |
|---|--|

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.