



# Smart line interactive USB UPS System - NAFTA assembled version of SMART750USB

# MODEL NUMBER: SM750UNAFTA





## **Description**

Tripp Lite's SM750UNAFTA line-interactive UPS system offers automatic voltage regulation, surge suppression and long lasting battery support. 750VA/450 watt power handling ability supports entry-level PCs, network workstations, point-of-sale equipment, small business phone systems, audio/video equipment and home theater systems. Internal UPS circuits support entry level PC systems for up to 45 minutes during power failures so that connected equipment can be shut down without data loss. Automatic Voltage Regulation (AVR) circuits regulate brownouts as low as 89 volts back to usable levels without using battery power. Offers complete desktop power protection in an attractive, black tower configuration. Includes 3 battery-supported outlets for computer, monitor and one vital system peripheral as well as 3 additional surge-only outlets for printers and other system accessories that do not require battery support. USB port (USB cable included) enables optional unattended system shutdown without data loss in the case of extended power failure. PowerAlert Software available via free download from www.tripplite.eaton.com. Built-in dataline protection jacks offer protection of a single dialup phone/DSL line or network Ethernet connection. Built-in audible alarm and 4 front panel LEDs indicate line power status, battery power status, battery low/replace status and voltage boost operation. Offers 3 minutes battery runtime with a full load of 750VA/450 watts and 11 minutes with a half load of 375VA/225 watts. Supports battery replacement via built-in access panel. \$200,000 Ultimate Lifetime Insurance (USA and Canada Only).

#### **Features**

- SM750UNAFTA line-interactive UPS system offers extended voltage regulation (AVR) and battery support as well as complete AC and dialup/DSL/Ethernet line surge suppression
- Supports entry level PC systems for up to 45 minutes during power failures to enable a safe system
- Supports a max load of 750VA/450 watts for 3 minutes and a half load of 375VA/225 watts for 11 minutes
- Automatic Voltage Regulation (AVR) circuits correct brownouts as low as 89 volts without using battery power
- Attractive black tower configuration

### **Highlights**

- 750VA line interactive tower UPS
- Maintains 120V nominal during brownout conditions
- Workstation optimized features include USB port, single line TEL / DSL or ethernet line surge suppression and three surgeonly outlets
- Input: NEMA 5-15P (120V 15A)
   / Output: 6 NEMA 5-15R (120V)
- \$200,000 Ultimate Lifetime Insurance (USA, Puerto Rico and Canada only)

# **Package Includes**

- SM750UNAFTA Standby UPS System
- USB and telephone interconnection cables
- Instruction manual with warranty information





- Includes 3 battery-supported outlets, plus 3 additional surge-only outlets, 6 foot AC line cord (all NEMA 5-15)
- USB port enables unattended shutdown without data loss during extended power failures; includes USB cable
- Built-in USB port supports on battery, low battery, power restored, AC line voltage, DC battery voltage
  and battery capacity messaging; interface supports timed inverter shutoff after unattended shutdown,
  activate self-test and 10 second reboot of connected equipment
- PowerAlert UPS monitoring and unattended shutdown software available via free download from tripplite.eaton.com
- Supports Tripp Lite's WatchDog software application to restore unresponsive programs by automatically restarting them and rebooting completely locked computers by automatically switching UPS power off and back on again (part #WATCHDOGSW)
- Built-in dataline suppression jacks protect a single dialup phone/DSL line or network Ethernet line connection.
- Built-in audible alarm and 4 front panel LEDs indicate UPS system and line power status
- 750VA/450 watt power handling ability supports a variety of computer, internetworking, telecom and consumer electronics equipment
- Supports battery replacement via built-in access panel
- Compatible with 120V/60Hz applications for USA, Canada, Mexico and more
- \$200,000 Ultimate Lifetime Insurance (USA and Canada Only)

# **Specifications**

OVERVIEW		
UPC Code	037332141316	
INPUT		
Rated input current (Maximum Load)	12A	
Nominal Input Voltage(s) Supported	120V AC	
UPS Input Connection Type	5-15P; Right-Angled	
UPS Input Cord Length (ft.)	6	
UPS Input Cord Length (m)	1.8	
Recommended Electrical Service	15A 120V	
ОИТРИТ		
Output Capacity (VA)	750	
Output Capacity (Watts)	450	
Frequency Compatibility	60 Hz	
Output Voltage Regulation (Battery Mode)	115V (+/- 5%)	
UPS Output Receptacles (Surge Suppression Only)	3 UPS outlets, 3 surge-only outlets	
Output AC Waveform (AC Mode)	Sine wave	
Output AC Waveform (Battery Mode)	PWM sine wave	





Nominal Output Voltage(s) Supported	115V; 120V
Output Receptacles	(6) 5-15R
BATTERY	
Runtime Full Load (min.)	3 min. (450w)
Runtime Half Load (min.)	11 min. (225w)
DC System Voltage (VDC)	12
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90%
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	<a class="productLink" href="//tripplite.eaton.com/UPS-Replacement-Battery-Cartridge-Tripp-Lite-APC-Belkin-Best-Powerware-Liebert-other-UPS~RBC51">RBC51"&gt;RBC51"&gt;RBC51</a>
Battery Replacement Description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with input voltage as low as 89
Undervoltage Correction	Input voltages between 89 and 104 are boosted by 14%
USER INTERFACE, ALERTS & COM	ITROLS
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions
LED Indicators	4 LEDs indicate line power, battery power, overload and battery low/replace status
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	480
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Primary Form Factor	Tower
Installation Form Factors Supported with Included Accessories	Tower
Installation Form Factors Supported with Optional Accessories	Wallmount ( <a class="productLink" href="//tripplite.eaton.com/Wall-Mount-Bracket-Installation-Accessories-for-UPS-Systems~UPSWM">UPSWM</a> - tower mounting kit)
Primary UPS Depth (mm)	191
Primary UPS Height (mm)	274
Primary UPS Width (mm)	132





Shipping Dimensions (hwd / in.)	14.00 x 8.50 x 10.50	
Shipping Dimensions (hwd / cm)	35.56 x 21.59 x 26.67	
Shipping Weight (lbs.)	16.50	
Shipping Weight (kg)	7.48	
UPS Housing Material	PVC	
UPS Power Module Dimensions (hwd, cm)	27.43 x 13.21 x 19.05	
UPS Power Module Dimensions (hwd, in.)	10.8 x 5.2 x 7.5	
UPS Power Module Weight (kg)	9.07	
UPS Power Module Weight (lbs.)	20	
ENVIRONMENTAL		
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius	
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius	
Relative Humidity	0 to 95%, non-condensing	
AC Mode BTU / Hr. (Full Load)	47.3	
AC Mode Efficiency Rating (100% Load)	97%	
Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	431.5	
COMMUNICATIONS		
PowerAlert Software	Free download from https://tripplite.eaton.com/products/power-alert	
Communications Cable	USB interface cable included	
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications	
Communications Interface	USB (HID enabled)	
LINE / BATTERY TRANSFER		
Transfer Time	2-4 milliseconds	
Low Voltage Transfer to Battery Power (Setpoint)	89	
High Voltage Transfer to Battery Power (Setpoint)	139	
FEATURES & SPECIFICATIONS		
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported	
High Availability UPS Features	Hot swappable batteries	
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS	
WARRANTY & SUPPORT		





Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.