

SmartRack 24U Mid-Depth Half-Height Rack Enclosure Cabinet

MODEL NUMBER: SR24UB



Houses, organizes and secures standard-depth 19 in. rack equipment in edge micro data centers and other mission-critical IT applications.

Features

Mid-Depth 24U Server Cabinet Accommodates 19 in. Rack Equipment

This SmartRack® 24U rack enclosure is designed for server rooms, IT closets, micro data centers, edge computing applications and other environments with essential rack-mount IT equipment. Constructed from heavy-duty steel with a durable black powder-coated finish, the SR24UB has a maximum stationary and rolling load capacity of 1,000 pounds (453 kilograms).

Keeps Important Equipment Secure

The reversible front and back doors and removable side panels lock securely to help prevent damage, tampering or theft. The doors and side panels are designed for quick release, making it simple to access connected equipment and cabling with little effort. Convenient top and bottom access panels allow easy cable routing through the cabinet. The vented doors and sides, as well as vents on the top and bottom, allow generous airflow from front to rear and top to bottom to keep your equipment cool and functioning at its peak.

Easy Enclosure and Equipment Installation

This 24U server rack comes fully assembled for quick and easy deployment. Front and rear vertical rails with square mounting holes accept standard rack equipment up to 32.5 inches (826 millimeters) deep. The top and bottom panels support installation of standard user-supplied case fans (such as SRFANWM, sold separately). Four metal casters with installation hardware allow you to maneuver the SR24UB over a level surface and through a standard doorway into position, where it can be stabilized by adjusting the included levelers. **Note:** The casters are intended for minor position adjustments within the final installation area only and are not designed for moving the enclosure over long distances.

Meets Payment Card Industry Standards

The SR24UB provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance. This is essential for companies that process, store and/or transmit credit card information.

Highlights

- 24U rack constructed from powder-coated steel that stands up to tough environments
- Maximum capacity: 1,000 lb. (453 kg) stationary and rolling load
- Doors and side panels lock securely to help prevent damage, tampering or theft
- Ships fully assembled for immediate deployment and equipment mounting
- Provides physical equipment and media security required for PCI DSS compliance

Package Includes

- SR24UB 24U Server Rack
- (50) M6 screws
- (50) M6 cage nuts
- (50) M6 washers
- (4) Casters
- (4) Levelers
- (2) Keys
- Owner's manual

Specifications

OVERVIEW



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--|--|
| UPC Code | 037332185228 |
| Device Compatibility | Patch Panel; Network Switch; UPS; Server |
| Rack Type | Half-Height Enclosure |
| PHYSICAL | |
| Color | Black |
| Rack Height | 24U |
| Rack Depth | Mid |
| Factory Preset Rack Depth (in.) | 28.31 |
| Factory Preset Rack Depth (cm) | 71.9 |
| Factory Preset Rack Depth (mm) | 719 |
| Maximum Device Depth (cm) | 82.55 |
| Maximum Device Depth (in.) | 32.5 |
| Maximum Device Depth (mm) | 826 |
| Minimum Device Depth (cm) | 7.62 |
| Minimum Device Depth (in.) | 3 |
| Minimum Device Depth (mm) | 76 |
| Cable Access Hole Measurement (inches) | 9.812 x 2.35 (l x w) |
| Shipping Dimensions (hwd / in.) | 52.00 x 26.00 x 35.00 |
| Shipping Dimensions (hwd / cm) | 132.08 x 66.04 x 88.90 |
| Shipping Weight (lbs.) | 172.00 |
| Shipping Weight (kg) | 78.02 |
| Unit Dimensions (hwd / in.) | 46.060 x 24.200 x 34.060 |
| Unit Dimensions (hwd / cm) | 115.82 x 60 x 85.09 |
| Unit Weight (lbs.) | 123 |
| Unit Weight (kg) | 55.79 |
| Weight Capacity - Rolling (kg) | 454 |
| Weight Capacity - Rolling (lbs.) | 1000 |
| Weight Capacity - Stationary (kg) | 454 |
| Weight Capacity - Stationary (lbs.) | 1000 |
| Number of Vertical Mounting Rails | 4 |
| FEATURES & SPECIFICATIONS | |
| Grounding Details | Front and Back door frames |
| Built-in Cable Management | Yes |
| Extra Wide | No |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|-------------------------------------|---------------------------|
| Locking | No |
| Pre-Installed Casters | No |
| Outdoor Use | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; EIA/ECA-310-E; UKCA |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 5-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.