

25U SmartRack 2-Post Open Frame Rack - Organize and Secure Network Rack Equipment

MODEL NUMBER: SR2POST25



Highlights

- 25U 2-post open frame rack
- Black aluminum with 12-24 threaded and numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

Package Includes

- SR2POST25
- 28 pieces each of 12-24 screws and washers for equipment mounting
- Installation hardware
- Cable management hooks
- Warranty Information
- Owner's Manual

Description

SR2POST25 2-Post SmartRack® Open Frame Rack is an economical way to accommodate 25U of rack space for 19-inch rack-mount applications in limited spaces that do not require a lockable enclosure. Its heavy-duty, aluminum construction can safely support 800 pounds (362.9 kilograms) of rack-mount equipment, and its open design provides easy access to equipment and cabling. The black, textured powder coat finish makes it resistant to scratching while giving it a "classic" attractive appearance. The SR2POST25 is easy to install due to a self-squaring design combined with 12-24 threaded and numbered mounting positions and bolt-down provisions. It uses toolless button-hole mounting for vertical PDUs and cable managers. In high-density environments, multiple units can be bolted together side by side for easy expansion or customization. The SR2POST25 2-Post SmartRack Open Frame Rack has been approved by EIA-310-D, IEC 60297-3-100 and RoHS.

Features

- Supports 800 lbs (362.9 kgs) of rackmount equipment
- Textured powder coat finish
- Heavy Duty Aluminum construction
- 12-24 threaded and numbered mounting positions
- Toolless button holes to accept PDUs or cable managers
- Bolt down provisions
- Self squaring design
- Black finish
- Easy assembly

Specifications

| OVERVIEW | |
|----------------------|--|
| UPC Code | 037332143143 |
| Device Compatibility | Patch Panel; Network Switch; UPS; Server |



Powering Business Worldwide



| | |
|--------------------------------------|--|
| Rack Type | Open-Frame |
| PHYSICAL | |
| Color | Black |
| Rack Height | 25U |
| Rack Depth | Extra Deep |
| EIA Mounting Rails | 12-24 threaded and numbered mounting positions |
| Maximum Device Depth (cm) | 121.92 |
| Maximum Device Depth (in.) | 48 |
| Maximum Device Depth (mm) | 1,219 |
| Shipping Dimensions (hwd / in.) | 4.50 x 6.00 x 52.60 |
| Shipping Dimensions (hwd / cm) | 11.43 x 15.24 x 133.60 |
| Shipping Weight (lbs.) | 26.00 |
| Shipping Weight (kg) | 11.79 |
| Unit Dimensions (hwd / in.) | 49.010 x 20.300 x 13.500 |
| Unit Dimensions (hwd / cm) | 124.46 x 51.56 x 12.06 |
| Unit Weight (lbs.) | 23 |
| Unit Weight (kg) | 10.43 |
| Weight Capacity - Stationary (kg) | 363 |
| Weight Capacity - Stationary (lbs.) | 800 |
| Number of Vertical Mounting Rails | 2 |
| Assembly Required | Yes |
| FEATURES & SPECIFICATIONS | |
| Pre-Installed Casters | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; EIA/ECA-310-E |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 5-year limited warranty |

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.