

## 45U SmartRack 4-Post Open Frame Rack - Threaded 12-24 Mounting Holes

MODEL NUMBER: SR4POST1224



### Highlights

- 45U 4-post open frame rack
- Black steel with threaded (12-24) mounted holes
- Toolless button holes to accept PDUs or cable managers

### Package Includes

- SR4POST1224
- Installation hardware
- 50x pieces of 12-24 screws and washers
- Cable management hooks
- Owner's Manual with warranty information

### Description

Tripp Lite's 45U 4-Post Open Frame Rack with Threaded Mounting Holes helps IT managers organize their equipment array and provides fast, easy access to installed IT equipment. The SR4POST1224 is a simple solution for housing IT equipment in secure environments and other areas that don't require a lockable rack solution. This 45U rack features heavy-duty cold-rolled steel construction with a black powder-coated finish for durability. It supports stationary loads up to 1000 lb. The SR4POST1224 comes with all the hardware required for assembly and has a self-squaring design with bolt-down provisions. For high-density applications, multiple units can be bolted together side by side.

The open design of the SR4POST1224 provides unobstructed airflow and easy access to equipment and cabling. It has threaded (12-24) mounting holes for easy installation of standard 19-inch rack equipment. The SR4POST1224 supports equipment depths from 22 to 36 inches. This rack also accommodates toolless button-hole mounting for vertical PDUs and cable managers.

### Features

- Supports 1000lbs of rackmount equipment
- Adjustable mounting depth (22 to 36 inches)
- Textured powder coat finish
- Heavy-duty cold-rolled steel construction
- Numbered mounting positions
- Bolt down provisions
- Threaded 12-24 holes
- Black finish
- Easy assembly



## Specifications

OVERVIEW	
UPC Code	037332159830
Device Compatibility	Patch Panel; Network Switch; UPS; Server
Rack Type	Open-Frame
PHYSICAL	
Color	Black
Maximum Device Depth (cm)	91.44
Maximum Device Depth (in.)	36
Maximum Device Depth (mm)	914
Minimum Device Depth (cm)	55.88
Minimum Device Depth (in.)	22
Minimum Device Depth (mm)	559
Rack Height	45U
Shipping Dimensions (hwd / cm)	11.18 x 16.76 x 224.54
Shipping Dimensions (hwd / in.)	4.40 x 6.60 x 88.40
Shipping Weight (kg)	33.57
Shipping Weight (lbs.)	74.00
Unit Dimensions (hwd / cm)	214.122 x 51.56 x 55.88 - 91.44
Unit Dimensions (hwd / in.)	84.3 x 20.3 x 22-36
Unit Weight (kg)	31.30
Unit Weight (lbs.)	69
Weight Capacity - Stationary (kg)	454
Weight Capacity - Stationary (lbs.)	1000
Rack Depth	Standard
Number of Vertical Mounting Rails	4
SPECIAL FEATURES	
Grounding Lug	Includes a set of screws, bolts, and washers to secure a user-supplied grounding wire to Front and Back frames
STANDARDS & COMPLIANCE	
Approvals	EIA-310-D, IEC 60297-3-100, RoHS
WARRANTY	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	5-year limited warranty
--	-------------------------

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>