

## 45U SmartRack 4-Post Open Frame Rack - Threaded 12-24 Mounting Holes

MODEL NUMBER: **SR4POST1224**



### Highlights

- 45U 4-post open frame rack
- Black steel with threaded (12-24) mounted holes
- Toolless button holes to accept PDUs or cable managers

### Package Includes

- SR4POST1224
- Installation hardware
- 50x pieces of 12-24 screws and washers
- Cable management hooks
- Owner's Manual with warranty information

### Description

This 45U 4-Post Open Frame Rack with Threaded Mounting Holes helps IT managers organize their equipment and provides fast, easy access to installed IT equipment. The SR4POST1224 is a simple solution for housing IT equipment in secure environments and other areas that don't require a lockable rack solution. This 45U rack features heavy-duty cold-rolled steel construction with a black powder-coated finish for durability. It supports stationary loads up to 1,000 pounds (453.6 kilograms). The SR4POST1224 comes with all the hardware required for assembly and has a self-squaring design with bolt-down provisions. For high-density applications, multiple units can be bolted together side by side. The open design of the SR4POST1224 provides unobstructed airflow and easy access to equipment and cabling. It has threaded (12-24) mounting holes for easy installation of standard 19-inch rack equipment. The SR4POST1224 supports equipment depths from 22 to 36 inches. This rack also accommodates toolless button-hole mounting for vertical PDUs and cable managers.

### Features

- Supports 1000 lbs (453.6 kgs) of rackmount equipment
- Adjustable mounting depth (22 to 36 inches)
- Textured powder coat finish
- Heavy-duty cold-rolled steel construction
- Numbered mounting positions
- Bolt down provisions
- Threaded 12-24 holes
- Black finish
- Easy assembly

## Specifications

OVERVIEW	
UPC Code	037332159830
Device Compatibility	Patch Panel; Network Switch; UPS; Server



Powering Business Worldwide



Rack Type	Open-Frame
<b>PHYSICAL</b>	
Color	Black
Rack Height	45U
Rack Depth	Standard
Maximum Device Depth (cm)	91.44
Maximum Device Depth (in.)	36
Maximum Device Depth (mm)	914
Minimum Device Depth (cm)	55.88
Minimum Device Depth (in.)	22
Minimum Device Depth (mm)	559
Shipping Dimensions (hwd / in.)	4.40 x 6.60 x 88.40
Shipping Dimensions (hwd / cm)	11.18 x 16.76 x 224.54
Shipping Weight (lbs.)	74.00
Shipping Weight (kg)	33.57
Unit Dimensions (hwd / in.)	84.300 x 20.300 x 39.400
Unit Dimensions (hwd / cm)	214.122 x 51.56 x 55.88 - 91.44
Unit Weight (lbs.)	69
Unit Weight (kg)	31.30
Weight Capacity - Stationary (kg)	454
Weight Capacity - Stationary (lbs.)	1000
Number of Vertical Mounting Rails	4
Assembly Required	Yes
<b>FEATURES &amp; SPECIFICATIONS</b>	
Grounding Details	Includes a set of screws, bolts, and washers to secure a user-supplied grounding wire to Front and Back frames
Pre-Installed Casters	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	IEC 60297-3
Product Compliance	RoHS; EIA/ECA-310-E
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty



*Powering Business Worldwide*



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.