

13U SmartRack 4-Post Open Frame Rack - Organize and Secure Network Rack Equipment

MODEL NUMBER: SR4POST13



Highlights

- 13U 4-post open frame rack
- Black steel with square, numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

Package Includes

- SR4POST13
- Installation hardware
- 16x M6 cagenuts, screws, washers
- 6x Cable management hooks
- Owner's manual with warranty information

Description

Tripp Lite's 13U 4-Post Open Frame Rack helps IT managers organize their equipment array and provides fast, easy access to installed IT equipment. The SR4POST13 is a simple solution for housing IT equipment in secure environments and other areas that don't require a lockable rack solution. This 13U rack features heavy-duty cold-rolled steel construction with a black powder-coated finish for durability. It supports stationary loads up to 1000 lb. The SR4POST13 comes with all the hardware required for assembly and has a self-squaring design with bolt-down provisions. For high-density applications, multiple units can be bolted together side by side.

The open design of the SR4POST13 provides unobstructed airflow and easy access to equipment and cabling. It has numbered, square-hole mounting positions for easy installation of standard 19-inch rack equipment. The SR4POST13 supports equipment depths from 22 to 36 inches. This rack also accommodates toolless button-hole mounting for vertical PDUs and cable managers.

Features

- Supports 1000lbs of rackmount equipment
- Adjustable mounting depth (22 to 36 inches)
- Textured powder coat finish
- Heavy-duty cold-rolled steel construction
- Numbered mounting positions
- Bolt down provisions
- Self squaring design
- Black finish
- Easy assembly



Specifications

OVERVIEW	
UPC Code	037332144041
PHYSICAL	
Rack Height	13U
Maximum Device Depth (in.)	36
Maximum Device Depth (cm)	91.44
Minimum Device Depth (in.)	22
Minimum Device Depth (cm)	55.88
Shipping Dimensions (hwd / in.)	4.53 x 6.50 x 48.62
Shipping Dimensions (hwd / cm)	11.51 x 16.51 x 123.49
Shipping Weight (lbs.)	41.90
Shipping Weight (kg)	19.01
Unit Dimensions (hwd / in.)	28 x 20.20 x 22-36
Unit Dimensions (hwd / cm)	71.12 x 51.3 x 55.9-91.44 (depth adjustable)
Unit Weight (lbs.)	39
Unit Weight (kg)	17.69
Color	Black
Weight Capacity - Stationary (lbs.)	1000
Weight Capacity - Stationary (kg)	454
Maximum Device Depth (mm)	914
Minimum Device Depth (mm)	559
SPECIAL FEATURES	
Grounding Lug	Includes nuts, bolts, and washers to attach to user-supplied ground wire
CERTIFICATIONS	
Approvals	EIA-310-D, IEC 60297-3-100, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>