

58U Heavy-Duty 4-Post SmartRack Open Frame Rack - Organize and Secure Network Rack Equipment

MODEL NUMBER: SR4POST58HD



Highlights

- 58U Heavy-Duty 4-post open frame rack
- Black steel with square, numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

Package Includes

- SR4POST58HD Heavy-Duty 4-Post Open Frame Rack
- Installation hardware
- (2x) PDU/Cable management brackets
- Owner's manual with warranty information

Description

This 58U Heavy-Duty 4-Post Open Frame Rack helps IT managers organize their equipment and provides fast, easy access to installed IT equipment. The SR4POST58HD is a simple solution for housing IT equipment in secure environments and other areas that don't require a lockable rack solution. This 58U rack features heavy-duty cold-rolled steel construction with a black powder-coated finish for durability. It supports stationary and rolling loads up to 3,000 pounds (1360.8 kilograms). The SR4POST58HD comes with all the hardware required for assembly and has a self-squaring design with bolt-down provisions. For high-density applications, multiple units can be bolted together side by side.

The open design provides unobstructed airflow and easy access to equipment and cabling. It has numbered, square-hole mounting positions for easy installation of standard 19-inch rack equipment. The SR4POST58HD supports equipment depths up to 35 inches. This rack also accommodates toolless button-hole mounting for vertical PDUs and cable managers.

The optional SRCASTERHDKIT Heavy-Duty Rolling Caster Kit (sold separately) adds mobility to the SR4POST58HD. The SR4POST58HD also supports optional side panels with the SR58SIDE4PHD, a set of two half-size side panels and a third smaller panel that add a finished look to end-of-row racks in your data center.

Features

- Weight capacity of 3000 lbs (1360.8 kgs) stationary
- Supports equipment depths up to 35 inches
- Textured, black powder coat finish
- Heavy-duty cold-rolled steel construction
- Numbered mounting positions
- Bolt down provisions
- Self-squaring design
- Easy assembly
- Optional SRCASTERHDKIT heavy-duty caster kit permits mobile use of 3000 lbs (1360.8 kgs) rolling loads
- Optional SR58SIDE4PHD side panels for end-of-the-row aesthetics

Specifications



Powering Business Worldwide



OVERVIEW	
UPC Code	037332185815
Device Compatibility	Patch Panel; Network Switch; UPS; Server
Rack Type	Open-Frame
PHYSICAL	
Color	Black
Rack Height	58U
Rack Depth	Standard
Maximum Device Depth (cm)	89.54
Maximum Device Depth (in.)	35.25
Maximum Device Depth (mm)	895
Shipping Dimensions (hwd / in.)	6.75 x 9.50 x 111.25
Shipping Dimensions (hwd / cm)	17.14 x 24.13 x 282.58
Shipping Weight (lbs.)	130.00
Shipping Weight (kg)	58.97
Unit Dimensions (hwd / in.)	107.500 x 24.000 x 35.250
Unit Dimensions (hwd / cm)	273.05 x 60.96 x 89.54
Unit Weight (lbs.)	125
Unit Weight (kg)	56.70
Weight Capacity - Stationary (kg)	1,361
Weight Capacity - Stationary (lbs.)	3000
Number of Vertical Mounting Rails	4
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Certifications	IEC 60297-3
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.