

## High-Capacity Vertical Cable Manager - Deep Double Finger Duct with Cover, Single Sided, 12 in. Wide, Black, 7 ft. (2.2 m)

MODEL NUMBER: SRCABLEVRT12HD



Vertical fiber cable manager routes and organizes network cabling through your open frame rack while maintaining proper bend radius.

### Features

#### 7 ft. Vertical Cable Manager Keeps Your Rack Looking Neat and Organized

Easy to mount along the side of your open frame rack, the SmartRack® SRCABLEVRT12HD neatly organizes fiber optic, copper and coax cable bundles. This vertical manager maintains proper bend radius to eliminate stress on the cables connecting your network devices. Fingers on either side allow convenient access to cabling for routing and separation of bundles. The high-capacity 12-inch (30.5-centimeter) width and 11.4-inch (29-centimeter) depth allows the installation and routing of large cable bundles. The cable manager is made from cold-rolled steel with a black finish to match your rack.

#### 3.5 ft. Sections Allow Flexibility in Mounting

The SRCABLEVRT12HD splits into two 3.5-foot (1.1-meter) sections to give you more installation options. All assembly hardware is included. No hardware is required for toolless 0U vertical installation in an EIA-standard 19-inch 2-post or 4-post open frame rack.

### Highlights

- Neatly organizes fiber, copper and coaxial cables in your 2- or 4-post open frame rack
- High-capacity 12 in. width allows installation and routing of larger cable bundles
- Splits into two 3.5 ft. sections to allow customization and multiple installation options
- Fingers and pass-through holes permit easy routing and separation of bundled cables
- Features button mounts for toolless installation in an EIA-standard 19 in. rack

### Package Includes

- (2) Door assemblies
- (4) Weldments
- (6) Tie plates
- (6) Cross brackets
- (4) Side panels
- (6) M4 x 6 flat-head screws
- (50) M4 x 8 tap screws
- (24) M4 x 8 pan-head screws
- (8) Door bushings
- (18) M4 x 12 pan-head screws
- (6) Mounting buttons
- (6) Mounting brackets
- (4) 1/2 in. hex bolts
- (4) 1/2 in. hex nuts
- (4) Metal spacers
- (4) 1/2 in. washers
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332239969
Accessory Type	Cable Management Accessories
PHYSICAL	
Color	Black

Shipping Dimensions (hwd / in.)	16.54 x 16.60 x 44.69
Shipping Dimensions (hwd / cm)	42.01 x 42.16 x 113.51
Shipping Weight (lbs.)	63.90
Shipping Weight (kg)	28.98
Unit Dimensions (hwd / in.)	82.820 x 12.080 x 13.400
Unit Dimensions (hwd / cm)	210.363 x 30.683 x 34.798
Unit Weight (lbs.)	57.000
Unit Weight (kg)	25.85
Cable Manager Form Factor	Vertical
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	EAC (Belarus, Kazakhstan, Russia); EIA/ECA-310-E; RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty