


# High-Capacity Vertical Cable Manager - Deep Double Finger Duct with Cover, Single Sided, 6 in. Wide, Yellow, 7 ft. (2.2 m)

MODEL NUMBER: SRCABLEVRT6HDFC



Vertical fiber cable manager routes and organizes network cabling through your open frame rack while maintaining proper bend radius.

## Features

### 7 ft. Vertical Cable Manager Keeps Your Rack Looking Neat and Organized

Easy to mount along the side of your open frame rack, the SmartRack® SRCABLEVRT6HDFC neatly organizes fiber optic, copper and coax cable bundles. This heavy-duty steel vertical manager maintains proper bend radius to eliminate stress on the cables connecting your network devices. Fingers on either side allow convenient access to cabling for routing and separation of bundles. The high-capacity six-inch (15.2-centimeter) width and 11.4-inch (29-centimeter) depth allows the installation and routing of large cable bundles. The high-visibility yellow finish helps you designate fiber-specific cable management spaces.

### 3.5 ft. Sections Allow Flexibility in Mounting

The SRCABLEVRT6HDFC splits into two 3.5-foot (1.1-meter) sections to give you more installation options. All assembly hardware is included. No hardware is required for toolless 0U vertical installation in an EIA-standard 19-inch 2-post or 4-post open frame rack.

## Highlights

- Neatly organizes fiber, copper and coaxial cables in your 2- or 4-post open frame rack
- High-capacity 6 in. width allows installation and routing of larger cable bundles
- Splits into two 3.5 ft. sections to allow customization and multiple installation options
- Fingers and pass-through holes permit easy routing and separation of bundled cables
- Features button mounts for toolless installation in an EIA-standard 19 in. rack

## Package Includes

- (2) Door assemblies
- (4) Weldments
- (6) Tie plates
- (6) Cross brackets
- (4) Side panels
- (6) M4 x 6 flat-head screws
- (50) M4 x 8 tap screws
- (24) M4 x 8 pan-head screws
- (8) Door bushings
- (18) M4 x 12 pan-head screws
- (6) Mounting buttons
- (6) Mounting brackets
- (4) 1/2 in. hex bolts
- (4) 1/2 in. hex nuts
- (4) Metal spacers
- (4) 1/2 in. washers
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332240033
Accessory Type	Cable Management Accessories
PHYSICAL	
Color	Yellow
Shipping Dimensions (hwd / in.)	16.54 x 12.60 x 44.69



Powering Business Worldwide



Shipping Dimensions (hwd / cm)	42.01 x 32.00 x 113.51
Shipping Weight (lbs.)	52.10
Shipping Weight (kg)	23.63
Unit Dimensions (hwd / in.)	82.820 x 6.080 x 13.700
Unit Dimensions (hwd / cm)	210.363 x 15.443 x 34.798
Unit Weight (lbs.)	47.00
Unit Weight (kg)	21.32
Cable Manager Form Factor	Vertical
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	EAC (Belarus, Kazakhstan, Russia); EIA/ECA-310-E; RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.