

# 10U ABS Server Rack Equipment Shipping Case

MODEL NUMBER: SRCASE10U



10U flight case lets you safely transport sensitive rack-mount equipment to trade shows, aboard airplanes or between facilities.

## Features

**10U Road Case Lets You Safely Transport Rack-Mount Equipment** This SmartRack® 10U flight case houses EIA-standard 19-inch rack equipment while it's being moved from one location to another. Constructed from heavy-duty ABS, the SRCASE10U features four stationary mounting rails that support up to 10U of servers, switches, patch panels, UPS systems and other rack components up to 20.5 inches deep. Maximum load capacity is 150 lbs (68 kgs). The case is ideal for transporting sensitive rack equipment to trade shows or other facilities without fear of damage.

**Protects Sensitive Devices against Moisture, Debris, Bumps and Jolts** This case comes fully assembled with a built-in handle on each side for convenient transportation. Once the device is mounted inside using the included hardware, both the front and rear covers with rubber gaskets are latched securely to keep out moisture, dust and other hazardous elements. A zippered pouch inside one cover stores extra hardware or other accessories. The SRCASE10U stacks securely with other identical cases.

## Highlights

- Fully assembled 10U ABS rack case for transporting equipment between facilities
- Stationary mounting rails allow secure installation using included hardware
- Latching front and rear covers designed to keep out moisture, dust and debris
- Interior zippered pouch allows storage of extra hardware and other accessories
- Mounts 10U of EIA-standard 19 in. rack equipment up to 20.5 in. deep and 150 lbs (68 kgs)

## Applications

- Safely transport 10U of rack-mount equipment to a trade show or a different facility
- Carry rack-mount DJ equipment, amplifiers and other professional audio gear to music venues

## Package Includes

- SRCASE10U 10U ABS Server Rack Equipment Flight Case
- (32) M5 screws
- (32) M5 cup washers

## Specifications

OVERVIEW	
UPC Code	037332210326
PHYSICAL	
Color	Black
Rack Height	10U
Maximum Device Depth (cm)	52.07
Maximum Device Depth (in.)	20.5
Maximum Device Depth (mm)	521
Shipping Dimensions (hwd / in.)	21.20 x 22.00 x 22.60



Powering Business Worldwide



Shipping Dimensions (hwd / cm)	53.85 x 55.88 x 57.40
Shipping Weight (lbs.)	21.00
Shipping Weight (kg)	9.53
Unit Dimensions (hwd / in.)	19.700 x 20.000 x 21.600
Unit Dimensions (hwd / cm)	50.4 x 50.8 x 54.86
Unit Weight (lbs.)	18.74
Unit Weight (kg)	8.50
Weight Capacity - Stationary (kg)	68
Weight Capacity - Stationary (lbs.)	150
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	EIA/ECA-310-E; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.