

2U ABS Server Rack Equipment Shipping Case

MODEL NUMBER: SRCASE2U



2U flight case lets you safely carry sensitive rack-mount equipment to trade shows, aboard airplanes or between facilities.

Features

2U Rack Flight Case Lets You Safely Transport Rack-Mount Equipment This SmartRack® 2U flight case houses EIA-standard 19-inch rack equipment while it's being moved from one location to another. Constructed from heavy-duty ABS, the SRCASE2U features four stationary mounting rails that support up to 2U of servers, switches, patch panels, UPS systems and other rack components up to 20.5 inches deep. Maximum load capacity is 50 lbs (22.7 kgs). The case is ideal for carrying sensitive rack equipment to trade shows or other facilities without fear of damage.

Protects Sensitive Devices against Moisture, Debris, Bumps and Jolts This 2U ABS rack case comes fully assembled with a built-in handle on each side for convenient carrying. Once the device is mounted inside using the included hardware, both the front and rear covers with rubber gaskets are latched securely to keep out moisture, dust and other damaging elements. A zippered pouch inside one cover stores extra hardware or other accessories. The SRCASE2U stacks securely with other identical cases.

Highlights

- Fully assembled 2U ABS rack case for transporting equipment between facilities
- Stationary mounting rails allow secure installation using included hardware
- Latching front and rear covers designed to keep out moisture, dust and debris
- Interior zippered pouch allows storage of extra hardware and other accessories
- Mounts 2U of EIA-standard 19 in. rack equipment up to 20.5 in. deep and 50 lb.

Applications

- Safely transport 2U of rack-mount equipment to a trade show or a different facility
- Carry rack-mount DJ equipment, amplifiers and other professional audio gear to music venues

Package Includes

- SRCASE2U 2U ABS Server Rack Equipment Flight Case
- (8) M5 screws
- (8) M5 cup washers

Specifications

OVERVIEW	
UPC Code	037332210357
PHYSICAL	
Color	Black
Rack Height	2U
Maximum Device Depth (cm)	52.07
Maximum Device Depth (in.)	20.5
Maximum Device Depth (mm)	521
Shipping Dimensions (hwd / in.)	6.90 x 22.00 x 22.50



Powering Business Worldwide



Shipping Dimensions (hwd / cm)	17.53 x 55.88 x 57.15
Shipping Weight (lbs.)	11.00
Shipping Weight (kg)	4.99
Unit Dimensions (hwd / in.)	5.500 x 20.000 x 21.600
Unit Dimensions (hwd / cm)	13.97 x 50.8 x 54.86
Unit Weight (lbs.)	9.26
Unit Weight (kg)	4.20
Weight Capacity - Stationary (kg)	23
Weight Capacity - Stationary (lbs.)	50
STANDARDS & COMPLIANCE	
Product Compliance	EIA/ECA-310-E; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.