

Wiring Closet Exhaust Fan, 475 CFM, NEMA 5-15P Input, Black

MODEL NUMBER: SRCLOSETFAN



Increases airflow inside your wiring closet to keep mission-critical equipment cool, boost system performance and avoid costly downtime.

Features

Increase Ventilation and the Flow of Fresh Air Through Your Enclosed Space This SmartRack® exhaust fan is ideal for maintaining a constant flow of air within your small wiring closet. Better airflow keeps your valuable rack components cool, helps boost system performance, and avoids costly equipment failures that lead to downtime, damage and data loss.

Powerful 120V Fans and Filter Provide a Proper Draft of Clean Air Two high-performance fans mount on either side of the wall of your wiring closet to either pull warm air from the inside or draw cool air from the outside. The high-speed ball-bearing 120V fans are capable of circulating air at 475 cubic feet per minute (CFM). The unit comes with a replaceable filter for keeping dust away from your electronic equipment.

Easy and Flexible Installation A mounting template is included for installing the SRCLOSETFAN between studs on walls up to eight inches thick. Mounting hardware is also included. The 15-ft. (4.57 m) power cord with NEMA 5-15P input is long enough to allow use in rooms with high ceilings. A convenient on/off switch allows one-touch control.

Highlights

- Dual high-performance 120V fans draw air through filtered panel at 475 CFM
- Supplies fresh filtered air and circulates it in a small confined area to cool equipment
- Includes hardware and template for mounting between wall studs in your wiring closet
- 15-ft. (4.57 m) cord with NEMA 5-15P input allows flexibility in connecting to AC power
- Convenient on/off switch allows simple one-touch control

Applications

- Draw warm air away from or pull cool air toward rack-mounted equipment to boost system performance, prevent costly downtime and extend operating life
- Prevent potentially harmful dust from circulating around your equipment
- Install 2 fans, one for inflow and one for outflow, for extra efficiency

Package Includes

- SRCLOSETFAN Wiring Closet Exhaust Fan
- Mounting template
- Mounting hardware
- Owner's manual

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332240651
INPUT	
Nominal Input Voltage(s) Supported	110V AC; 120V AC
Nominal Input Voltage Description	110-120V 50/60Hz
Input Plug Features	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
COOLING	
Cooling Type	Active
Airflow	475 CFM
PHYSICAL	
Shipping Dimensions (hwd / in.)	10.30 x 16.60 x 20.70
Shipping Weight (kg)	13.24
Shipping Weight (lbs.)	29.20
Unit Dimensions (hwd / cm)	17.78 x 32.7025 x 43.815
Unit Dimensions (hwd / in.)	7.000 x 12.875 x 17.250
Unit Weight (kg)	9.80
Unit Weight (lbs.)	21.610
SPECIAL FEATURES	
Sound Level (Noise)	65 dB
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>