

SmartRack Magnetic Vinyl Kit for Rack Airflow Management

MODEL NUMBER: SRCOOLMVKIT



Passive airflow containment kit blocks vented panels of an EIA-standard 19 in. rack enclosure to prevent cool air from escaping and help connected equipment last longer and operate more efficiently.

Description

The SRCOOLMVKIT SmartRack® Magnetic Vinyl Kit consists of six panels that attach magnetically to the vented front door, rear door or side panel of your floor or wall-mount rack enclosure. By blocking perforated areas, cool air is trapped inside the rack cabinet, and hot spots that can damage connected equipment are eliminated. Operating at a cooler temperature allows your sensitive rack equipment to last longer and work more efficiently. With four 16.9 x 18.8-inch and two 16.9 x 5.2-inch magnetic vinyl panels, the SRCOOLMVKIT can cover an EIA-standard 19-inch 48U rack door perforation pattern. It is compatible with all SmartRack enclosures.

Features

Traps Cool Air Inside SmartRack Enclosure for Maximum Cooling Efficiency

- 6 magnetic panels attach to vented rack doors and side panels
- Blocks perforated areas to prevent cool air from escaping
- Seals tightly to eliminate hot spots that can harm equipment
- Covers up to a standard 48U rack door perforation pattern
- Compatible with all SmartRack enclosures

Highlights

- 6 magnetic panels attach to vented rack doors and side panels
- Traps cool air inside rack for maximum cooling efficiency
- Seals tightly to eliminate hot spots that can harm equipment
- Covers a standard 48U rack door perforation pattern
- Compatible with all SmartRack enclosures

Package Includes

- (4) Magnetic vinyl panels, 16.9 x 18.8 in.
- (2) Magnetic vinyl panels, 16.9 x 5.2 in.

Specifications

OVERVIEW	
UPC Code	037332255037
Accessory Type	Airflow Management
Accessory Class	Cooling Accessories
COOLING	
Cooling Type	Passive



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Shipping Dimensions (hwd / in.)	0.60 x 18.90 x 20.50
Shipping Dimensions (hwd / cm)	1.52 x 48.01 x 52.07
Shipping Weight (lbs.)	7.00
Shipping Weight (kg)	3.18
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.