

9U Air Inlet Duct Kit - Nexus 7000-Series Switches and Tripp Lite Wide Racks

MODEL NUMBER: SRDUCTN7009



Pulls cool air from the front of the rack and directs it to your Cisco Nexus 7000-Series switch or other equipment requiring concentrated ducting.

Features

Improves Your Cisco Nexus 7000-Series Switch's Performance by Keeping It Cool This SmartRack rack-mount ducting kit pulls cool air from the front of the rack and directs it toward the rear exhaust of your Cisco Nexus switch. Dual tray ducts direct cool airflow on the top and bottom of the switch, and two boxes direct airflow to the sides. The side boxes create a concentrated exhaust pathway to prevent warm air from recirculating back to the rack's cold-aisle side. This extra airflow keeps your switch cool to ensure it maintains peak performance.

Easy to Install Efficiently with Included Hardware The SRDUCTN7009 is designed for extra-wide 750-millimeter Tripp Lite racks, including SRW6UDPVRT and SRW9UDPVRT, and does not fit standard-width racks. All necessary mounting hardware is included for hassle-free setup that saves you time and money on installation. The 9U unit is designed specifically to accept Cisco Nexus 7000 switches, but its modular and spacious design can also house other equipment that requires concentrated ducting.

Highlights

- Designed to keep your Cisco Nexus 7000-Series network switch cool
- 9U duct kit forces cool air toward switch's rear exhaust for better airflow
- Features 2 tray ducts (top and bottom) and side inlet and exhaust box ducts
- Includes all necessary mounting hardware for efficient, immediate installation
- Designed to mount into extra-wide 750 mm Tripp Lite SmartRack® racks

Applications

- Increase airflow around your Cisco Nexus switch or other compatible rack equipment to maintain peak performance

System Requirements

- Specifically geared for Cisco Nexus 7000 Series switches
- Mounts into extra-wide 750 mm Tripp Lite racks
- Does not fit standard-width SmartRack racks

Package Includes

- Inlet box
- Exhaust box
- Top tray
- Bottom tray
- (16) M6 x 16 screws
- (16) M6 cup washers
- (7) M4 screws
- (2) Rear plates



- Assembly instructions

Specifications

OVERVIEW	
UPC Code	037332196439
COOLING	
Cooling Type	Passive
PHYSICAL	
Shipping Dimensions (hwd / cm)	67.49 x 26.49 x 95.00
Shipping Dimensions (hwd / in.)	26.57 x 10.43 x 37.40
Shipping Weight (kg)	36.29
Shipping Weight (lbs.)	80.00
STANDARDS & COMPLIANCE	
Certifications	EIA-310-E
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>