


# Toolless Trumpet Drop-Out Kit for Fiber Routing System, 120 mm (5 in.)

MODEL NUMBER: SRFC5DROP



Raceway trumpet spillout narrows your fiber optic cables to a standard 2 in. bend radius when exiting a channel or vertical T.

## Features

### High-Impact PVC Drop-Out Helps You Create Custom Fiber Cable Routing Schemes

The SmartRack® SRFC5DROP limits the bend radius of your fiber optic cabling to two inches (50 mm) as it exits from a channel, horizontal T fitting or vertical T. A proper two-inch bend radius protects against signal loss and damage to the cables. Made from durable, lightweight PVC material, this trumpet drop-out connects using the included hardware to help keep your cable bundles neat and organized. Screws and nuts tighten by hand with no tools required to complete a professional, finished look in your data center, network closet or industrial space.

## Highlights

- Allows you flexibility in creating your custom fiber optic cable routing system
- Constructed from durable but lightweight PVC plastic
- Easy to install with your fiber routing system with no tools needed

## Applications

- Create a fiber routing system along the wall or ceiling of your data center or network closet or across the tops of the rack enclosures

## System Requirements

Requires a 5 in. or 120 mm wide section from Fiber Routing System

## Package Includes

- Trumpet dropout, 120 mm
- (4) T-shaped screws
- (4) Twist nuts
- Installation guide

## Specifications

OVERVIEW	
UPC Code	037332240903
Product Type	Dropout
Accessory Type	Cable Management Accessories
Cable Management System Component Type	Drop Out/Waterfall
PHYSICAL	
Color	Yellow
Shipping Dimensions (hwd / in.)	2.80 x 5.70 x 7.80
Shipping Weight (kg)	0.23
Unit Dimensions (hwd / in.)	4.920 x 7.000 x 2.800
Unit Dimensions (hwd / cm)	12.5 x 17.78 x 7.11



Powering Business Worldwide



Unit Weight (lbs.)	0.291
Unit Weight (kg)	0.13
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; EIA/ECA-310-E
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.