

SmartRack Adjustable-Deep Steel Rack Shelf - 1U, Vented, 250 lb. (113 kg) Capacity

MODEL NUMBER: SRSHELF4PHDVENT



Vented shelf adjusts to house a wireless access point and other non-rack devices to save space in your server room or network closet.

Features

1U Vented Rack Shelf Secures Non-Rack Equipment in Your Data Center

This SmartRack® adjustable-depth shelf supports monitors, wireless access points, tower units and other IT equipment not typically stored in a rack. Made from heavy-duty cold-rolled steel with a durable black powder-coated finish, the SRSHELF4PHDVENT has a maximum load capacity of 250 pounds (113 kilograms). It mounts easily into 1U of space in an EIA-standard 19-inch 4-post enclosure or open frame rack using the included hardware.

Maximizes Rack Space and Saves Desk or Floor Space in a Busy Office

The steel shelf is 25.38 inches (64.5 centimeters) deep for organizing network and other non-rack equipment in your small office or server room. The vented surface allows generous airflow to keep your equipment cool and functioning at its peak. The side brackets are easily adjustable to the depth of your rack from 25.94 inches (65.9 centimeters) to 40.75 inches (103.5 centimeters).

Specifications

OVERVIEW	
UPC Code	037332263131
Accessory Type	Rack Shelves
Accessory Class	Rack Accessories
PHYSICAL	
Unit Dimensions (hwd / in.)	1.730 x 19.000 x 26.100
Unit Dimensions (hwd / cm)	4.39 x 48.26 x 66.29
Unit Weight (lbs.)	16.5

Highlights

- Adjustable 1U rack shelf secures non-rack equipment like WAPs and monitors
- Heavy-duty cold-rolled steel construction with maximum load capacity of 250 lb. (113 kg.)
- Vented design maximizes airflow to protect equipment against excessive heat
- Side brackets adjust to the depth of your 4-post rack from 25 in. to 40.75 in.

Package Includes

- SRSHELF4PHDVENT 1U Shelf with Adjustable Mounting Brackets
- (8) M6 screws
- (8) M6 cup washers
- (8) M6 cage nuts
- Instruction sheet



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Weight (kg)	7.48
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>