

SmartRack Thermal Duct Kit for SmartRack Enclosures

MODEL NUMBER: SR THERMDUCT



Need to help your equipment perform at its peak while reducing your facility's cooling and energy cost? The SR THERMDUCT kit can change a standard Tripp Lite SmartRack 42-48U enclosure into sealed passive cooling structure that allows heat that is exhausted from equipment to be vented upwards into the facility CRAC / HVAC air return system.

Description

The SR THERMDUCT Thermal Duct Kit can change a standard SmartRack 42-48U enclosure into a sealed passive cooling structure that allows heat built up inside a rack to be directed up and into the facility CRAC / HVAC return air system.

Features

- Improves cooling efficiency of standard rack enclosures
- Adjustable roof-mount thermal duct connects to HVAC return air system
- Included gaskets and panels help seal enclosure for proper airflow management through thermal duct
- Compatible with standard 42-48U SmartRack Enclosures

Highlights

- Improves cooling efficiency in standard rack enclosures
- Adjustable roof-mounted thermal duct moves air upward and out of the rack enclosure
- Compatible with standard 42-48U SmartRack Enclosures

System Requirements

Standard 42-48U Rack Enclosure

Package Includes

- Height-adjustable roof-mount thermal duct
- Roof-mount cable access panel
- Enclosure bottom
- Door gasket seals
- (16) Magnetic vinyl sheet rear door seals
- (4) M8 screws
- (4) M4 screws
- (16) M4 nuts
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332154903
Accessory Type	Duct Kit
Accessory Class	Rack Accessories
COOLING	
Cooling Type	Passive
PHYSICAL	
Housing Color	Black



Powering Business Worldwide



Roof	Thermal duct adjusts between 20.5-34.5 inches when assembled.
Shipping Dimensions (hwd / in.)	14.57 x 23.62 x 47.64
Shipping Dimensions (hwd / cm)	37.01 x 59.99 x 121.01
Shipping Weight (lbs.)	67.00
Shipping Weight (kg)	30.39
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.