

SmartRack 15U Low-Profile Switch-Depth Wall-Mount Half-Height Rack Enclosure, Clear Acrylic Window, Hinged Back

MODEL NUMBER: **SRW15USG**



Wall-mount cabinet secures and organizes 15U of 19-inch rack equipment in network closets, classrooms and other locations with limited floor space. Clear acrylic window allows you to monitor equipment without unlocking door.

Description

The SRW15USG SmartRack 15U Low-Profile Switch-Depth Wall-Mount Rack Enclosure Cabinet is ideal for storing EIA-standard 19-inch rack equipment in network closets and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 200 lbs (90.7 kgs).

The front door features a shatter-resistant clear acrylic window that lets you monitor equipment readouts without unlocking the enclosure. Not only does the window help prevent equipment tampering and reduce acoustic noise, but it also adds visual flair to your IT installation.

The cabinet swings away from the wall on a sturdy hinge, allowing easy access to equipment and cabling during installation and maintenance. To ensure your valuable equipment stays secure, the doors and side panels lock. The top, bottom and removable side panels are vented, which allows air to flow freely through the rack to keep equipment cool. The reversible doors can open left or right by rotating the cabinet 180° before mounting. Convenient top and bottom ports allow easy cable routing through the cabinet.

The SRW15USG comes fully assembled and ready to mount to the wall. Square and 12-24 threaded mounting holes and numbered rack spaces make equipment installation easy. The vertical mounting rails adjust in 7/8-inch increments to house equipment up to 20.5 inches deep, such as network switches and patch panels.

Features

Saves Valuable Workspace

- Perfect for network closets, retail locations, classrooms and other areas with limited floor space where you need equipment to be secure, organized and out of the way
- Houses EIA-standard 19 in. rack equipment in 15U of space
- Maximum load capacity of 200 pounds (90.7 kg)

Hinged Cabinet for Convenient Access

- Swings away from the wall to allow easy access to equipment and cabling during installation and maintenance
- Rotate cabinet 180° before mounting to open reversible front door left or right

Highlights

- Maximum load capacity of 200 lbs (90.7 kgs)
- Swings away from wall bracket on a hinge for easy access
- Front door includes shatter-resistant clear acrylic window
- Locking steel cabinet vented at sides, top and bottom
- Secures 15U of 19 in. rack equipment up to 20.5 in. deep

Package Includes

- SRW15USG SmartRack 15U Low-Profile Switch-Depth Wall-Mount Rack Enclosure Cabinet
- (20) M6 screws
- (20) M6 cage nuts
- (20) M6 washers
- (20) 12-24 screws
- (2) Keys
- Owner's manual

Shatter-Resistant Clear Acrylic Front Window

- Lets you monitor equipment without unlocking the enclosure
- Prevents equipment tampering
- Reduces acoustic noise
- Provides extra visual flair

Keeps Important Equipment Secure

- Side panels and front door lock securely
- Vented panels allow generous airflow that keeps equipment cool
- Convenient ports with removable covers allow cable routing through top and bottom

Easy Enclosure and Equipment Installation

- Ships fully assembled for quick installation
- Mounts to wall or rolls on floor with optional SRCASTER caster kit
- Wall-mounting holes spaced 16 in. apart to accommodate standard wall stud placement
- Vertical mounting rails adjust in 7/8 in. increments to house equipment up to 20.5 in. deep
- Rails support square-hole or 12-24 threaded-hole mounting
- Rack spaces numbered for easy reference

Meets Payment Card Industry Standards

- Provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

Specifications

| OVERVIEW | |
|---------------------------------|----------------------------------|
| UPC Code | 037332187369 |
| Device Compatibility | Patch Panel; Network Switch; UPS |
| Rack Type | Half-Height Enclosure |
| PHYSICAL | |
| Color | Black |
| Rack Height | 15U |
| Rack Depth | Shallow |
| Factory Preset Rack Depth (in.) | 10.42 |
| Factory Preset Rack Depth (cm) | 26.5 |
| Factory Preset Rack Depth (mm) | 265 |
| Maximum Device Depth (cm) | 52.07 |
| Maximum Device Depth (in.) | 20.5 |
| Maximum Device Depth (mm) | 521 |



Powering Business Worldwide



| | |
|--------------------------------------|----------------------------|
| Minimum Device Depth (cm) | 7.62 |
| Minimum Device Depth (in.) | 3 |
| Minimum Device Depth (mm) | 76 |
| Shipping Dimensions (hwd / in.) | 24.10 x 33.07 x 26.38 |
| Shipping Dimensions (hwd / cm) | 61.21 x 84.00 x 67.01 |
| Shipping Weight (lbs.) | 75.00 |
| Shipping Weight (kg) | 34.02 |
| Unit Dimensions (hwd / in.) | 30.330 x 23.620 x 21.600 |
| Unit Dimensions (hwd / cm) | 77.04 x 60 x 54.86 |
| Unit Weight (lbs.) | 88.2 |
| Unit Weight (kg) | 40.01 |
| Weight Capacity - Stationary (kg) | 91 |
| Weight Capacity - Stationary (lbs.) | 200 |
| Number of Vertical Mounting Rails | 4 |
| FEATURES & SPECIFICATIONS | |
| Grounding Details | Front and Back door frames |
| Pre-Installed Casters | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; EIA/ECA-310-E; UKCA |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 5-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.