

## SmartRack 6U Low-Profile Switch-Depth Knock-Down Wall-Mount Mini Rack Enclosure

MODEL NUMBER: SRW6UKD



Wall-mount cabinet secures and organizes 6U of 19 in. rack equipment in network closets, classrooms and other locations with limited floor space. Houses network switches and patch panels up to 16.5 in. deep.

### Description

The SRW6UKD SmartRack® 6U Low-Profile Switch-Depth Knock-Down Wall-Mount Rack Enclosure Cabinet is designed to house EIA-standard 19-inch rack equipment in network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 200 lbs (90.7 kgs).

The front door locks securely to help prevent damage, tampering and theft. The front, top, bottom and side panels are vented, which allows air to flow freely and keep equipment cool. The reversible front door can be installed to open left or right. Convenient top and bottom ports allow easy cable routing.

The SRW6UKD comes unassembled for convenient transport and storage in confined spaces. It easily assembles in minutes using just 12 fasteners, and mounts to the wall to save valuable floor space. Square and 12-24 threaded mounting holes and numbered rack spaces make equipment installation easy. The vertical mounting rails adjust in 7/8-inch increments to accommodate equipment up to 16.5 inches deep, such as network switches and patch panels.

### Features

#### Saves Valuable Workspace

Perfect for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Houses EIA-standard 19 in. rack equipment in 6U of space. Maximum load capacity of 200 lbs (90.7 kgs).

#### Keeps Important Equipment Secure

Front door locks securely to help prevent damage, tampering and theft. Vented panels allow generous airflow that keeps equipment cool. Reversible front door can be installed to open left or right. Convenient ports with removable covers allow cable routing through top and bottom.

#### Ships Unassembled

Knock-down shipping for convenient transport and storage in confined spaces. Assembles in minutes using just 12 fasteners. Wall-mounting holes spaced 16 in. apart for standard wall stud placement.

#### Easy Equipment Installation

Vertical mounting rails adjust in 7/8 in. increments to accommodate equipment up to 16.5 in. deep, such as network switches and patch panels. Rails support square-hole or 12-24 threaded-hole mounting. Rack spaces numbered for easy reference.

### Highlights

- Ships unassembled for easy transport and storage
- Maximum load capacity of 200 lbs (90.7 kgs)
- Locking steel cabinet vented at sides, front, top and bottom
- Flow-through ventilation keeps equipment cool
- Mounts to wall to save valuable floor space

### Package Includes

#### Assembly Hardware

(2) Top/bottom panels (2) Side panels Front door (2) Vertical mounting rails (24) M6 screws (4) M6 cage nuts (4) M6 cup washers (2) Keys

#### Equipment Mounting Hardware

(12) 12-24 screws (12) M6 cage nuts (12) M6 cup washers

- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

#### Meets Payment Card Industry Standards

Provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

## Specifications

OVERVIEW	
UPC Code	037332191564
Device Compatibility	Patch Panel; Network Switch; UPS
Rack Type	Small Enclosure
PHYSICAL	
Color	Black
Rack Height	6U
Rack Depth	Shallow
Maximum Device Depth (cm)	41.91
Maximum Device Depth (in.)	16.5
Maximum Device Depth (mm)	419
Minimum Device Depth (cm)	7.62
Minimum Device Depth (in.)	3
Minimum Device Depth (mm)	76
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Shipping Dimensions (hwd / in.)	25.98 x 20.28 x 7.08
Shipping Dimensions (hwd / cm)	65.99 x 51.51 x 17.98
Shipping Weight (lbs.)	30.00
Shipping Weight (kg)	13.61
Unit Dimensions (hwd / in.)	14.449 x 23.630 x 17.547
Unit Dimensions (hwd / cm)	36.7 x 60.02 x 44.57
Unit Weight (lbs.)	29
Unit Weight (kg)	13.15
Weight Capacity - Stationary (kg)	91
Weight Capacity - Stationary (lbs.)	200
Number of Vertical Mounting Rails	2
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Grounding Details	Front and Back door frames



Powering Business Worldwide

TRIPP LITE  
SERIES

Built-in Cable Management	No
Extra Wide	No
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 60950-1
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.