

SmartRack 6U Low-Profile Switch-Depth Knock-Down Wall-Mount Rack Enclosure Cabinet

MODEL NUMBER: SRW6UKD



Wall-mount cabinet secures and organizes 6U of 19 in. rack equipment in network closets, classrooms and other locations with limited floor space. Houses network switches and patch panels up to 16.5 in. deep.

Description

The SRW6UKD SmartRack® 6U Low-Profile Switch-Depth Knock-Down Wall-Mount Rack Enclosure Cabinet is designed to house EIA-standard 19-inch rack equipment in network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 200 pounds.

The front door locks securely to help prevent damage, tampering and theft. The front, top, bottom and side panels are vented, which allows air to flow freely and keep equipment cool. The reversible front door can be installed to open left or right. Convenient top and bottom ports allow easy cable routing.

The SRW6UKD comes unassembled for convenient transport and storage in confined spaces. It easily assembles in minutes using just 12 fasteners, and mounts to the wall to save valuable floor space. Square and 12-24 threaded mounting holes and numbered rack spaces make equipment installation easy. The vertical mounting rails adjust in 7/8-inch increments to accommodate equipment up to 16.5 inches deep, such as network switches and patch panels.

Features

Saves Valuable Workspace

- Perfect for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way
- Houses EIA-standard 19 in. rack equipment in 6U of space
- Maximum load capacity of 200 lb.

Highlights

- Ships unassembled for easy transport and storage
- Maximum load capacity of 200 lb.
- Locking steel cabinet vented at sides, front, top and bottom
- Flow-through ventilation keeps equipment cool
- Mounts to wall to save valuable floor space

Package Includes

- Owner's manual

Assembly Hardware

- (2) Top/bottom panels
- (2) Side panels
- Front door
- (2) Vertical mounting rails
- (24) M6 screws
- (4) M6 cage nuts
- (4) M6 cup washers
- (2) Keys

Equipment Mounting Hardware

- (12) 12-24 screws
- (12) M6 cage nuts
- (12) M6 cup washers



Keeps Important Equipment Secure

- Front door locks securely to help prevent damage, tampering and theft
- Vented panels allow generous airflow that keeps equipment cool
- Reversible front door can be installed to open left or right
- Convenient ports with removable covers allow cable routing through top and bottom

Ships Unassembled

- Knock-down shipping for convenient transport and storage in confined spaces
- Assembles in minutes using just 12 fasteners
- Wall-mounting holes spaced 16 in. apart for standard wall stud placement

Easy Equipment Installation

- Vertical mounting rails adjust in 7/8 in. increments to accommodate equipment up to 16.5 in. deep, such as network switches and patch panels
- Rails support square-hole or 12-24 threaded-hole mounting
- Rack spaces numbered for easy reference

Meets Payment Card Industry Standards

- Provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

Specifications

OVERVIEW	
UPC Code	037332191564
Device Compatibility	Patch Panel; Network Switch
Rack Type	Enclosure
PHYSICAL	
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Color	Black
Maximum Device Depth (cm)	41.91
Maximum Device Depth (in.)	16.5
Maximum Device Depth (mm)	419
Minimum Device Depth (cm)	7.62
Minimum Device Depth (in.)	3
Minimum Device Depth (mm)	76



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Rack Height	6U
Shipping Dimensions (hwd / cm)	65.99 x 51.51 x 17.98
Shipping Dimensions (hwd / in.)	25.98 x 20.28 x 7.08
Shipping Weight (kg)	13.61
Shipping Weight (lbs.)	30.00
Unit Dimensions (hwd / cm)	36.7 x 60.02 x 44.57
Unit Dimensions (hwd / in.)	14.45 x 23.63 x 17.94
Unit Weight (kg)	13.15
Unit Weight (lbs.)	29
Weight Capacity - Stationary (kg)	91
Weight Capacity - Stationary (lbs.)	200
Rack Depth	Shallow
Number of Vertical Mounting Rails	2
SPECIAL FEATURES	
Grounding Lug	Front and Back door frames
STANDARDS & COMPLIANCE	
Certifications	UL/CSA 60950-1, EIA-310-E; IP20 Protection Rating
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>